






PAPT NO	TS3025-X-X	
Operating Force	160 : 160gf ; 260 : 260gf	
Height	15 : 1.5mm	17 : 1.7mm
	16 : 1.6mm	

技术参数

1. 额定电流:50mA 12V DC
2. 接触电阻:100毫欧
3. 行程:0.15±0.05mm
4. 绝缘电阻:100兆欧
5. 抗电强度:100v 50Hz 1Min



电器原理图



P C B 参考图

		new		2015/5/3		A		瀚源
ECN BO.		DESCRIPTION.		DATE.		REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	TS3025-X-X		UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25	
			MODEL NAME	TS3025-X-X			X.x ±0.20	
			3RD ANGLE PROJ	HanElectricity Co.,LTD			X.xx ±0.15 ANGULAIR ±3	
			FILE.NO.					