




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



SPECIFICATIONS

- Current rating: 1A AC, DC
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 100MΩ Min.
- Withstanding voltage: 250V AC/ minute.
- Contact resistance: 20mΩ Max.


Material:

Insulator: LCP UL 94V-0
 Contact: Brass
 Solder Tab: Brass
 Plating: Matte Tin or gold plated over Nickel
 Circuits: 2~08
 Mate with: XFCN P1250 series Housing
 Ordering Code:

M1250VS-XX-LP

材质: LP=LCP
 Pin位数 2=02P
 8=08P

No. of PIN/ROW	Dimension	
	A	B
2	1.25	7.20
3	2.50	8.45
4	3.75	9.70
5	5.00	10.95
6	6.25	12.20
7	7.50	13.45
8	8.75	14.70



PCB LAYOUT

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: M1250VS-xx-LP		XFCN 兴飞连接器	
TITLE: 1.25mm Crimp Style Connectors		0769-82001899	
		www.xfconn.com	
		DWG NO: /	
APPD	Chen ZhiQiang	VIEW	
CHKD	Liu Wei	SCALE	SHEET
DRAW	Chen HongJiang	SCALE	REV
DATE	2024.05.24	NONE	1:1 A1