








3D VIEW



PART INSTRUCTIONS:

PART NUMBER	DESCRIPTION
SIM304-ZYD7AH1.37	WITH POST
SIM304-ZYB7AH1.37	NO POST

NOTES:

1.MATERIAL:

HOUSING: High Temperature Thermoplastic

Terminal:Copper Alloy

Shell: Stainless Steel

2.PLATING:

Terminal:50u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

Shell:30u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

3.technical speciality:

RATED VOLTAGE: 30V AC MAX.

CURRENT RATING: 0.5A MAX.

INSULATION RESISTANCE:1000MΩ MIN

CONTACT REISTANCE:50mΩ MAX

WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTES


OPERATING TEMPERATURE:

-25℃~+85℃ Humidity 80% R.H MAX

4.DIMENSIONS WITH MARK" * "MUST BE MEASURE


BY QC AND IPQC

PIIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
CD	Detect Switch
C5	GND
C6	VPP
C7	I/O



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	.X*±5°	APR. Alex	TITLE: 1.37H 6+1PIN PUSH NANO SIM CARD CONNECTOR		
.XX±0.25	.X*±3°	CHK. Jack	DWG NO. SIM304-ZYB7AH1.37		
			PROJ. 		
.XXX±0.15	.XX*±1°	DRA. Can	CUSTOMER DRAWING		
			SIZE A4	SCALE 1:1	SHEET 1/2

厦门市辛译精密电子有限公司
Xiamen XinYi Xyecom Electronics Co.,Ltd



2	SIM304-ZYD7AH1.37	1500	10		15000	350X350X340
1	SIM304-ZYB7AH1.37	1500	10		15000	350X350X340
ITEM	PRODUCT NO	QTY/REEL	REEL/CARTON	Kg/CARTON	QTY/CARTON	CARTON SIZE

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	.X°± 5°	APR. Alex	TITLE: 1.37H 6+1PIN PUSH NANO SIM CARD CONNECTOR		
.XX±0.25	.X°± 3°	CHK. Jack	DWG NO. SIM304-ZYB7AH1.37		
.XXX±0.15	.XX°± 1°	DRA. Can	PROJ.	CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 2/2