

Specification Sheet

Part Number: 151-03040

One-piece ratchet closure allows for easy installation during pre- or final assembly.

Easy release feature simplifies quick adjustments and maintenance.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.

Zinc-plated steel mounting plate tolerates high torque and is treated to resist chemicals and salt spray.

Straight, 180° mounting plate is ideal for applications requiring a flush mount set off from the mounting hole.



Ratchet P-Clamp, 0.76 - 1.42" Bundle Dia, 180° Short, 0.41" Hole Dia, PA66HIRHSUV/ST/ZN, Black, 20/bg

Article Number	151-03040
Type	RCC180SM10
Color	Black (BK)
Quantity Per	bag
Product Description	Ratchet P-Clamp, 0.76 - 1.42" Bundle Dia, 180° Short, 0.41" Hole Dia, PA66HIRHSUV/ST/ZN, Black, 20/bg
Short Description	Ratchet P-Clamp, 0.76 - 1.42" Bundle Dia, 180° Short, 0.41" Hole Dia, PA66HIRHSUV/ST/ZN, Black, 20/bg

Global Part Name	RCC180SM10-PA66HIRHSUV/ST/ZN-BK
------------------	---------------------------------

Minimum Tensile Strength (Imperial)	100.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	445
-----------------------------------	-----

Length L (Imperial)	6.15
---------------------	------

Length L (Metric)	156.1
-------------------	-------

Fixation Method	Screw Mounting
-----------------	----------------

Variant	Short
---------	-------

Width W (Imperial)	1.37
--------------------	------

Width W (Metric)	34.9
------------------	------

Bundle Diameter Min (Imperial)	0.76
--------------------------------	------

Bundle Diameter Min (Metric)	19.4
------------------------------	------

Bundle Diameter Max (Imperial)	1.42
--------------------------------	------

Bundle Diameter Max (Metric)	36.0
------------------------------	------

Mounting Hole Diameter D (Imperial)	0.405
-------------------------------------	-------

Mounting Hole Diameter D (Metric)	10.29 mm
-----------------------------------	----------

Stud Diameter (Metric)	M10
------------------------	-----

Mounting Hole Centers (Imperial)	2.45
Material	Steel (ST) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Zinc plated (ZN)
Material Shortcut	ST PA66HIRHSUV ZN
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Plenum Rating	AH-2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	20
Package Quantity (Metric)	20

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).