



Powering Business Worldwide

Cat5e 350 MHz Snagless Molded Ethernet Cable (RJ45 M/M) - Gray, 125-ft.

MODEL NUMBER: N001-125-GY



Description

Tripp Lite's 125-ft. gray snagless category 5e (Cat5e) patch cable has 2 snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair Solid Conductor UTP for improved long run performance, and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Standard category 5e patch cables are also available.

Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 125-ft. Color: gray Connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair Solid UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available - Cat6 cables (N201 series)

Highlights

- Cabling for Category 5 (Cat5) and 5e (Cat5e) applications
- Solid Conductor wire for long distance performance
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation
- Feature molded connectors with integral strain relief. Rated for 350 MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 5e, draft 11)

System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

Package Includes

- 125-ft. Gray Snagless Cat5e Patch Cable

Specifications

OVERVIEW	
UPC Code	037332041951
Technology	Cat5/5e
CONNECTIONS	



Powering Business Worldwide

Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
PHYSICAL	
Color	Gray
Cable Shielding	UTP
Wire Type	Solid
Cable Length (ft.)	125
Cable Length (m)	38.11
Cable Length (in.)	1500
Cable Length (cm)	3810
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 2.00
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 5.08
Shipping Weight (lbs.)	2.80
Shipping Weight (kg)	1.27
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
FEATURES & SPECIFICATIONS	
Snagless Connector	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.