

6

5

4

3

2



1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/15/23	
A		UPDATE DRAWING	3/24/23	LH/RC

Part Number	Nominal Size(mm)	busbar dimension	As supplied(mm)	After recovered(mm)		Applicable busbar dimension (mm)		Standard Length (Meter)
			I.D.(min) (D)	I.D.(max) (d)	W.T.(w)	L+T(min)(max)	R(min)(max)	
HST-B-020-RD-X-24KV	20	20x3	20±0.8	10	2.5±0.5	13~28	11~18	(Whole Reel) 25 Meter
HST-B-030-RD-X-24KV	30	30x3, 30x4	30±0.8	13	2.5±0.5	22~38	13.5~25	
HST-B-040-RD-X-24KV	40	30x10, 40x4	40±1	16	2.5±0.5	25~40	17~37	
HST-B-050-RD-X-24KV	50	40x10, 50x5, 50x6	50±2	20	2.5±0.5	36~65	22~43	(Whole Reel) 20 Meter
HST-B-065-RD-X-24KV	65	50x8, 50x10, 60x6, 60x8	65±3	25	3.0±0.5	39~70	27~56	
HST-B-080-RD-X-24KV	80	60x10, 80x10	80±3	31	3.0±0.5	55~95	33~70	
HST-B-100-RD-X-24KV	100	100x8, 100x10, 100x12	100±4	40	3.0±0.5	70~130	44~86	
HST-B-120-RD-X-24KV	120	100x15, 120x10 120x12, 120x15	120±4	50	3.0±0.5	90~165	55~105	
HST-B-150-RD-X-24KV	150	150x12, 150x15	150±4	60	3.5±0.5	95~180	70~135	
HST-B-180-RD-X-24KV	180	150x10, 150x20	180±5	75	3.5±0.5	125~235	80~150	



HST-B-XXX-RD-X-24KV

TYPE SEE CHART

Color= RED

Length
R= Whole Reel
A= 1.22 meters

SPECIFICATIONS:

Material: Polyolefin

Electrical:

Shrinkage: 2.5:1

Dielectric withstanding voltage: 24KV

Temperature Rating:

Operating temperature: -45°C to +105°C

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN	WX	3/15/23
CHECKED	RC	3/15/23
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM
TECH**909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
BUSBAR INSULATING HEAT SHRINK TUBING
WITHSTAND VOLTAGE UP TO 24KV

SIZE	PART NO.	REV.
X	HST-B-XXX-RD-X-24KV	-
REF:	S00303T	SCALE: NTS SHEET 1 OF 1