




1. 产品外观光滑，平整，不得有划伤残缺等不良现象
2. 所有材质符合ROHS环保要求
3. 耐压60VDC,额定电流5A，耐高温120℃
4. 插拔力5-30N, 寿命5000次
5. “*”重点管控尺寸

				TOLERANCE UNLESS SPECIFIED								
				UP TO 5mm:±0.1	ANGULAR	A0	2019.12.31	首次发行		GYW		
				ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
				TITLE: DC JACK				UNIT : MM	ROHS	DWN		
3	RTC30-02BPU+PB 2#	PBS/PBT	1	Ag PLATED/BLACK				MODEL: RT-C30-BA-1	SCALE: 6:1	COMPLIANT	CHK'D	
2	RTC30-01BPU-PIN 1#	PBS	1	Ag PLATED				东莞市六钧电子五金有限公司				
1	RTC30-BAPB-B00	PBT	1	BLACK								
NO.	PART NAME	MATERIAL	QTY	FINISHING								
									PRO.AGL:			REV :A0