







#### Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:4A AC/DC

额定电流: 4A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃-+105℃





温度范围: -40℃-+105℃

Insulation resistance:1000MΩ min


绝缘电阻: 1000MΩ Min

Contact resistance:30mΩ Max


接触电阻: 30mΩ Max




2x02 Pin




2x03 Pin




2x04 Pin




2x05 Pin



2x06 Pin



2x07 Pin



2x08 Pin

X2513 H - 2xXX X - 46  
① ② ③ ④ ⑤

1.Series No

2.Category:H-HSG

3.Row No.Pin No:2xXX-2x02~2x12 Pin

4.Special No: A:Key A (Black)

B:Key B (Natural)

5.Material:46-Nylon 46+30%G.F UL94V-0

| Poles | Dimensions(mm) |
|-------|----------------|
|       | A              |
| 2x02  | 7.70           |
| 2x03  | 10.20          |
| 2x04  | 12.70          |
| 2x05  | 15.20          |
| 2x06  | 17.70          |
| 2x07  | 20.20          |
| 2x08  | 22.70          |
| 2x12  | 32.70          |

|                 |                    |                       |                          |
|-----------------|--------------------|-----------------------|--------------------------|
| X2513H-2xXXA-46 | Nylon<br>46+30%G.F | X2513W                | X2513T                   |
| X2513H-2xXXB-46 |                    |                       |                          |
| PART NO         | Material           | Suitable XKB<br>Wafer | Suitable XKB<br>Terminal |

|      |  |             |                                            |
|------|--|-------------|--------------------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:<br>2.5mm Crimp Style Connector |
| DWN  |  | VIEW:       | PART NO.:<br>X2513H-2xXXX-46               |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-X2513H-2xXXX-46              |
| APPD |  | SIZE: A4    |                                            |

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|        |       |          |
|--------|-------|----------|
| WEIGHT | SHEET | REVISION |
|        | 1/1   | A0       |

广东星坤科技股份有限公司

|      |       |
|------|-------|
| Δ建   | 日期    |
| Δ改   |       |
| ΔX   |       |
| MARK | 文件工程章 |

DESCRIPTION

DATE

REVISED

APPROVED

REVISIONS

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.com www.xk-dg.cn