

1

2



3

4





5

6

ZONE	REV.	DESCRIPTION	APPROVED	DATE
	B	2007ECR/N0148		
	C	2015ECR/N0039		2015-09-16



PANEL CUT OUT



CIRCUIT: DPDT

SPECIFICATIONS:


Rating: DC 12V 2.7A (Inrush Current 16A)
Maximum Snap-in Mounting Force: 18Lbs (8.2kg)
Button Depression Force: 2.0Lbs (228~912g)
Cycle life single: 130,000 cycles 0.65s ON/0.65s OFF

9	MovABLE SPRING HOLDER	NYLON66	1	BLACK
8	CONTACTOR	AgSn02	8	NATURAL
7	SPRING	SWPB	2	NI PLATED
6	CONTACT BRIDGE	BRASS	2	Ag PLATED
5	CENTER TERMINAL	BRASS	2	Ag PLATED
4	EDGE TERMINAL	BRASS	4	Ag PLATED
3	HOUSING	NYLON66	1	BLACK
2	COVER	NYLON66	1	BLACK
1	PLASTIC KNOB	NYLON66	2	WHITE
NO.	PART NAME	MATERIAL	QTY.	FINISHING

TOLERANCES UNLESS OTHERWISE STATED

DIMENSIONAL ±0.2
ANGULAR ±3°

PROJECTION



DO NOT SCALE THIS DRAWING

DRAWN CHECKED APPROVED

东莞市六钧电子五金有限公司

TITLE ROCKER SWITCH

MODEL PS2238-N3X00FP040NW

P/N

DATE 2015-09-16

REV. C

UNIT : mm

SCALE :

SIZE : A4