





HAOYU



USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B7	Dn2
A6	Dp1	B6	Dp2
A7	Dn1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
DEFAULT TOLERANCE: ± 0.05

TOLERANCE UNLESS SPECIFIED											
		UP TO 5mm: ± 0.1	ABOVE 5mm: ± 0.2	ANGULAR $\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD	
5		COVER		SUS	1						
4		FRONT SHELL		SUS	1	Ni-PLATED	TITLE: USB JACK		UNIT : MM	ROHS	
3		MID PLATE		SUS	1		MODEL: USB-307L-B-SU-1 T2.0		SCALE: 1:1	COMPLIANT	
2		TERMINAL		COPPER ALLOY	14	Au/Ni-PLATED				CHK'D	
1		HOUSING		PA9T(UL94V-0)	1					APPD	
NO.	PART	NAME	MATERIAL	QTY	FINISHING		东莞市六钧电子五金有限公司			PRO.AGL:  	REV :AO