




P.C.B LAYOUT
TOP VIEW



SCHEMATIC



H	2.0	3.0	4.0	5.0	6.0	7.0	8.0	9.0	10.0
						✓			

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		REVISIONS			BY	APPD
						UP TO 5mm: ±0.1	ANGULAR ±1°	NO	DATE	ROHS COMPLIANT	DWN	CHK'D
6	CONTACT CLIP	PBS		1	Ag-PLATED			1				
5	SPRING PLATE	SUS/PBS		1	Ag-PLATED	ABOVE 5mm: ±0.2	±1°					
4	CONTACT FOOT	BRASS		3	Ag-PLATED							
3	BOTTOM	PF		1								
2	BUTTON	POM/PA66		1								
1	COAT	IRON		1	Ni-PLATED							
东莞市六钧电子五金有限公司										APPD		
										PRO.AGL:	◆	◆
										REV :A0		