





PCB. LAYOUT

1. 电路 CIRCUIT: ON/OFF
2. 额定值 RATING: 5A 30VDC (UL;CUL)
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘阻抗 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINTUTE
6. 柄的颜色ACTUATOR COLOR: 黑色BLACK
基座的颜色HOUSING COLOR: 黑色BLACK
7. 所有部件均使用环保材料
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE



OPEN CIRCUIT



CLOSED CIRCUIT
(PLUG IN)

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2020.11.14	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.10	LEGION ELECTRONIC & HARDWARE CO., LTD.				SS01-BBI-1+DC-005-1		*****	A0
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'								