


Model No.	POS.1	POS.2	POS.3
2AS4	MOM	OFF	MOM
Term. Comm.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



P.C. MOUNTING

▲克重200±100g

SPECIFICATIONS

MECHANICAL LIFE: 50,000 make-and-break cycles.
CONTACT RESISTANCE: 20 mΩ max. initial @ 2-4VDC
 100mA for both silver and gold plated contacts.
INSULATION RESISTANCE: 1,000 MΩ min.
DIELECTRIC STRENGTH: 1,000 Vrms min. @sea level.
OPERATING TEMPERATURE: -30°C to 85°C.

MATERIALS

CASE & BUSHING - Glass filled nylon 6/6 , retardant ,
 heat stadiilized(UL94V-0)
ACTUATOR - Brass, chrome platede.Internal O-ring seal. standard
 for all actuators.
TERMINALS/CONTACT - Copper.
RoHS & Lead Free

	CONTACT PLATING	TERMINAL PLATING	RATINGS
Q	Silver	Q = Gold flash over silver	3 Amps @120 VAC or 28VDC 1 Amps @250 VAC
S		S = Gold flash over silver,pure-tin	
C	Gold over Silver	C = Gold over silver	
K		K = Gold over silver,pure-tin	
R	Gold	R = Gold	0.4 Volt-Amps(VA) max @20V max. (AC or DC)
G		G = Gold,pure-tin	

东莞市六钧电子五金有限公司

符號	原尺寸	修改後尺寸	變更日期	SCALE (比例): 3:2	TITLE	圖名	SIZE	
1	克重200±50g	克重200±100g	FEB/03/2015	TOLERANCE (公差): 0.00 mm ± 0.25mm 0.0 mm ± 0.40mm ANGULAR : ± 5° FILE NAME : 2ASP0431	Sealed Sub - Miniature Toggle Switches	圖紙	A4	
2					DWG NO.	2AS4T1A1M2RES	UNIT	inch
3					REV.	B	DATE	JAN - 08 - 2015
4					CHECKED BY	RICHARD	DRAWN BY	IRENE
5					審核		製圖	