







					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

K 137635 H M - 2xXX B - N0
① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x08 Pin
- 6.Material:N0-PA66 UL 94V-0






K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector
DWN	VIEW:	PART NO.: K137635HM-2xXXB-N0
CHKD	UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0




					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED



Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Temperature range:-40℃-+125℃
 温度范围: -40℃-+125℃



K 137635 H M - 2xXX B - N0
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x10 Pin
- 6.Material:N0-PA66 UL 94V-0


K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector		
DWN		VIEW: 	PART NO.: K137635HM-2xXXB-N0		
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
L PRECISION CO.,LIMITED				1/1	A0


					ANGLAR	±5°
Δ X					L≤ 4	±0.2
Δ X					4<L≤ 16	±0.3
Δ X					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED




Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃



K 137635 H M - 2xXX B - N0
 (1) (2) (3) (4) (5) (6) (7)



1.K: XKBTEK-Car Connector
2.XKB Series No
3.Category:H-Housing
4.Category:M-Male Housing
5.Row No.Pin No:2xXX-2x14 Pin
6.Material:N0-PA66 UL 94V-0



K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal


DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector		
DWN		VIEW: 	PART NO.: K137635HM-2xXXB-N0		
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0		
APPD		SIZE: A4			
L. PRECISION CO., LIMITED			WEIGHT	SHEET 1/1	REVISION A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxb.com www.helloxb.cn www.xk-dg.cn						

[illegible]





K 137635 H M - 2xXX B - N0
 (1) (2) (3) (4) (5) (6) (7)

Technical drawing of a stepped shaft. The drawing shows a shaft with a central section of diameter 10 mm and two end sections of diameter 12 mm. The total length of the shaft is dimensioned as 38.3 [1.520] ± 0.3. The drawing is a side view with a centerline indicating the axis of symmetry.



DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector		
DWN		VIEW: 	PART NO.: K137635HM-2xXXB-N0		
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0		
APPD		SIZE: A4			
PRECISION CO., LIMITED			WEIGHT	SHEET 1/1	REVISION A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

K 137635 H M - 2xXX B - N0
① ② ③ ④ ⑤ ⑥ ⑦


- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x18 Pin
- 6.Material:N0-PA66 UL 94V-0

K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector
DWN		VIEW:	PART NO.: K137635HM-2xXXB-N0
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0
APPD		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
			SHEET
			REVISION
			1/1
			A0



					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						





K 137635 H M - 2xXX B - N0
 (1) (2) (3) (4) (5) (6) (7)

1.K: XKBTEK-Car Connector
2.XKB Series No
3.Category:H-Housing
4.Category:M-Male Housing
5.Row No.Pin No:2xXX-2x20 Pin
6.Material:N0-PA66 UL 94V-0



K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector
DWN		VIEW: 	PART NO.: K137635HM-2xXXB-N0
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0
APPD		SIZE: A4	

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dq.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0