






NOTES

(1) MATERIAL: SUS-304 THICKNE=0.10mm

(2)PRODUCT SPECIFICATIONS:

2-1:RATED CURRENT: 1.0A

2-2:VOLTAGE RATING: 1.50V

2-3:CONTACT RESISTANCE: 80mΩ/MAX

2-4:WELDING THRUST: $\geq 3\text{KG}$

2-5: OPERATING TEMPERATURE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$

2-6:DURABILITY: 1500 CYCLES

(3):SALT SPRAY: 24 HOURS


(4):FINISH:50u"Min NICKEL UNDERPLATING OVER ALL.

(5):REQUIREMENTS


5-1:TERMINAL TO EAT FULL TIN,NOTPEELING

WELDING OBVIOUS COLOR AND OTHER ADVERSE

5-2:ROHS,REACH,HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT

TOLERANCE ± 0.05 (焊盘推荐图)

深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY :		DATE :		PART NAME:	
X.X ±0.30		陈一鸣		2014-02-23		天线弹片 L2.80*W1.5*H1.1	
X.XX ±0.25		CHECKED BY:		DATE :		PART NO.	
X.XXX ±0.15						HYCW-TXT281511A	
X: ±2° X.X° ±0.5°		马跃		2014-02-23		MOLD NO.	
						APPROVED BY:	
		HYC-2406061205					
UNIT: mm [inch]		邱敏		2014-02-23		SHEET NO.	
SCALE:1:1 SIZE: A4						1 OF 1	