

承認書

SPECIFICATION FOR APPROVAL

CUSTOMER: _____ 2144 _____


DESCRIPTION: _____ COMMON MODE CHOKE _____

DDY PART NO: _____ WBA1008D系列 _____

CUSTOMER MODEL NO: _____

DRAWING		
MADE	CHECKED	APPROVED
譚晶晶	黃志偉	肖中華
DATE:		

CUSTOMER APPROVE



惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD


廣東省博羅縣洲際工業園梅園三路
NO.3 MEI YUAN ROAD, ZHOU JI INDUSTRIAL AREA, BOLUO COUNTY GUANGDONG

電話： 15970768093 13640935893

傳真：0752-6207969

郵編：516100

Http://ddycoils.com




惠州市德立电子有限公司

HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:		REV NO:	A
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 1 OF 8
PART NO:	WBA1008D系列	SN.	
CUSTOMER NO:		DATE:	

CATALOG

Resume	P2
Shape & Dimension	P3
Part numbering ststem	P3
General specification	P3
Electrical Characteristics List	P4
Soldering Conditions	P5
Material List	P5
Package Information	P6
Package Specifications	P7
Electrical Characteristic Curve	P8



惠州市德立电子有限公司


HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:		REV NO:	A
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 4 OF 8
PART NO:	WBA1008D系列	SN.	
CUSTOMER NO:		DATE:	

4. Electrical Characteristics List

NO.	Part Number	Z	Freq	Rdc	Irms	Rated Voltage	Insulation Resistance			
		(Ω)	(MHz)	(Ω) Max	(mA) Max	Volts	(MΩ) Min			
1	WBA1008D301PT-F-HF	300	100	0.20	400	50	10			
2	WBA1008D451PT-F-HF	450	100	0.30	350	50	10			
3	WBA1008D601PT-F-HF	600	100	0.38	330	50	10			
4	WBA1008D102PT-F-HF	1000	100	0.50	240	50	10			

APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶




惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:		REV NO:	A
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 5 OF 8
PART NO:	WBA1008D系列	SN.	
CUSTOMER NO:		DATE:	

5. SOLDERING CONDITIONS


**Figure 1.
Re-flow Soldering
(Lead Free)**



Note:

- Preheat circuit and products to 150°C
- 260°C tip temperature (max)
- Reflow times: no more than 2 times
- Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

**Figure 2.
Hand Soldering**



Note:


- Use a 20 watt soldering iron with tip diameter of 1.0mm
- Limit soldering time to 3 sec.

6.MATERIAL LIST

NO	DESCRIPTION	DESCRIPTION	SUPPLIER	
1	Upper Plate	Ferrite	Flag Magnetic Or equivalent	
2	Core	Ferrite Core	Flag Magnetic Or equivalent	
3	Wire	Enameled Copper Wire	Elektrisola Or equivalent	

REMARK:

APPROVED BY	CHECKED BY	DRAWN BY
肖中华	黄志伟	谭晶晶




惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:		REV NO:	A
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 6 OF 8
PART NO:	WBA1008D系列	SN.	
CUSTOMER NO:		DATE:	

7. PACKAGING(unit: mm)

Type	1008
Quantity	2000


TAPING DRAWINGS




REEL DIMENSIONS(UNIT:mm)

	A	B	C	N	G
CF-12	178±2.0	22±2.0	12.5±1.5	57±2.0	12

LEADER AND BLANK PORTION



PEELLING OFF FORCE:0.05 to 0.7N in the direction show below.



APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶






惠州市德立电子有限公司

HUI ZHOU DE LI ELECTRONICS CO., LTD

CUSTOMER:		REV NO:	A
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 7 OF 8
PART NO:	WBA1008D系列	SN.	
CUSTOMER NO:		DATE:	

8.Package Specifications

■Inside Box And Outside Carton




卷轴数量	内盒包装数量	外箱包装数量
每卷:2000 PCS	每盒四盘, 共8000 PCS	每箱6盒, 共48000 PCS
		每箱8盒, 共64000 PCS
		每箱10盒, 共80000 PCS

注意:

此物料不涉及汽车或相关产品方面的应用, 否则, 由此引起的一切品质和责任问题, 我司将概不承担。

APPROVED BY	CHECKED BY	DRAFT
肖中华	黄志伟	谭晶晶




惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD


CUSTOMER:		REV NO:	A
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 8 OF 8
PART NO:	WBA1008D系列	SN.	
CUSTOMER NO:		DATE:	

9. ELECTRICAL CHARACTERISTIC CURVE


WBA1008D301PT-F-HF




WBA1008D451PT-F-HF



WBA1008D601PT-F-HF



WBA1008D102PT-F-HF



APPROVED BY

肖中华

CHECKED BY

黄志伟

DRAFT

谭晶晶