



P.C.B LAYOUT(Top view)



Rating: 5A 24V DC
 Contact Resistance: 100 mΩ Max.
 Operating temperature: -25°C ~ 80°C
 Operating force: 3~20N
 Operating Life: 5,000cycles



Model No.	DC-005E-20A	DC-005E-25A
PIN	Ø2.0	Ø2.5

③	PIN	1	Brass	Sn Plating			
②	Terminal	3	Phosphor bronze/Brass	Ag Plating			
①	Housing	1	PPA	Black	UL 94V-0		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING		
APPROVALS				REMARK			
DRAWN	LIUCAN	2023.9.19		TITLE: 阻燃款宽脚5A电流			
APPROVALS							
TOLERANCES ARE				PART NO.	DC-005E		
				ANGLE	UNIT: mm		
30~以上		±0.30	10~30	±0.20	SCALE: 1:1		
5~10		±0.15	~ 5	±0.10	PROJ: 		
DRAWING NO.				SHEET 1 OF 1			



—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.