







ROHS

Http://www.krhro.com



DC MATE PLUG

Rating: 5A 24V DC
Contact Resistance: 100 mΩ Max.
Operating temperature: -25℃~80℃
Operating force: 3~20N
Operating Life: 5,000 cycles



P.C.B LAYOUT(Top view)

Model No.	DC-005E-20A	DC-005E-25A
PIN	Ø2.0	Ø2.5

③	PIN	—	1	Brass	Sn Plating	—
②	Terminal	—	3	Phosphor bronze/Brass	Ag Plating	—
①	Housing	—	1	PPA	Black	UL 94V-0
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN		LIUCAN	2023.9.19				
CHECKED					TITLE:	阻燃款宽脚5A电流	
APPROVALS					PART NO.	DC-005E	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2'		DRAWING NO.	_____		SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.