



规格说明:Specifications:

电气特性: Electrical:

- 1. 额定电流: Current Rating
5.0A/contact terminal
 - 2. 额定电压: Voltage Rating
30V DC
 - 3. 接触阻抗: Contact Resistance
30 milliohms MAX
 - 4. 耐电压: Dielectric Withstanding Voltage:
500V AC/1KV DC

物理性能: Mechanical

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)

原材料:Material:

- ## 1. 塑胶:Housing: Hing Temperature Thermaplastics,

2. 端子: Contact: Copper Alloy C2680

3.外殼:Shell: Copper Alloy C2680/SPCC

电镀:Finish:

1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails

端子四周镀50U”(MIN)锡,镀金区域镀100-200U”镀金1U”

2.外殼:Shell:
外殼四周鍍80U”(MIN)鍍

Nickel Plating

						APPROVALS		DATE				
		DRAWN	LIUCAN	2023.4.13								
		CHECKED				TITLE:		大电流5A				
		APPROVALS				PART NO.		U-A-24DD-Y-8D				
	A	NEW				TOLERANCES ARE 30~以上 10~30 5~10 ~ 5		±0.30 ±0.25 ±0.20 ±0.15	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
ECN NO.	REV.	DATE.	DESCRIPTION.		CHANGE.			CHECK.	APPRO.	±2°	DRAWING NO.	——