



FILE: 02/





Kinghelm®

REV	CONTENT	CHK	DATE
V0.0	CONTENT		2014-11-20



NOTES:

1. Rating: 300V 15A ;
2. Insulation Withstands Voltage: AC2000V/MIN
3. Insulation Resistance: 500MΩ or more at DC500V
4. Using Temperature Range: -40°C~+105°C
5. "★" is the important dimension

**SECTION:A-A**

DIM	2	3	4	5	6	7	8	9	10	xxx	24
L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	xxx	121.92
A	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	xxx	116.84

A	Total Pitch Tolerances in mm									Nominal dimension range in mm										⊥	≡	—	//							
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320											
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10											
	±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2											
6									5										0.2		0.3		0.3		0.2		0.3		0.5	

ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL			NOTE	
DWG.		DATE	2014-11-20	SIZE	A4	UNITS	mm	SHEET/OF	1 / 1
CHK.		DATE		SCALE	3:1			5.08	
APP.		DATE		NAME					
深圳市金航标电子有限公司			www.kinghelm.com.cn						
KH-F400V-2P-5.08G			0755-28190160	DWGNO.					