


建议PCB板厚1.0~1.2mm



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

H	PART NO.
1.30	TYPE-C-31-M-19
1.70	TYPE-C-31-M-19A

③	Shell	—	1	STAINLESS STEEL	Ni Plated
②	Contact	—	14	COPPER ALLOY	Au Plated
①	Housing	—	1	LCP	Black
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS			DATE				
DRAWN	JIANKUN.LU	2018.08.01		TITLE:			USB CONNECTOR
CHECKED					PART NO.		
APPROVALS					TOLERANCES ARE		
			30~以上	±0.30	ANGLE	UNIT: mm	
			10~30	±0.25	±2'	SCALE: 1:1	
			5~10	±0.20		DRAWING NO.	
			~ 5	±0.15		PROJ:	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.