





Kinghelm®



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

SPECIFICATION

1 Material:

Insulator: PA66 (UL94V-0)

Contacts: Brass, Gold-plated

2 Contact resistance: $\leq 20\text{m}\Omega$

3 Insulation resistance: $\geq 1000\text{M}\Omega$

4 Rated voltage: 250 V AC DC

5 Rated current: 2.5 A AC DC

6 Withstand Voltage: 800V AC/minute

7 Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

8 Six deleterious substance content
meet the environmental protection
requirement

				TOLERANCE	SCALE:	2510-A	
				, ±0.25	UNIT: mm	TITLE: 2.54mm PITCH 90° WAFER	PART NO:
				*,** ±0.15	VIEW:		
				*,*** ±0.05			
				DRAW			
				CHECK			
A	NEW RELEASE			APPRO		深圳市金航标电子有限公司	www.kinghelm.com.cn
REV	DESCRIPTION	REV. DRAWN	DATE			KH-HX2.54-05Z	0755-28190160