








PCB Layout(Pattern Side)



Circuit Diagram



LED colour(LED颜色)	Part No. (料号)
Whiler(白色)	K6-8859D-01
Red(红色)	K6-8859D-02
Blue(蓝色)	K6-8859D-03
Green(普绿)	K6-8859D-04

Typical Specifications

- 1.Rating : DC 12V 50mA
- 2.Operating Force : 250 ± 50 gf
- 3.Contact Resistance : 100mΩMAX
- 4.Life : 100,000 Cycles Min

⑦	LED	—	1	—	Transparent	—
⑥	Keystoke	—	1	PA66	White	—
⑤	Spring	—	1	Keystoke	Ag	—
④	Base	—	1	PA66	Black	—
③	Cover	—	1	PA66	Black	—
②	Terminal	—	6	Phosphor bronze	Ag Plating	—
①	Housing	—	1	Nylon	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS

DATE

DRAWN

D.J.LV

2017/12/26

CHECKED

APPROVALS

TITLE:

LED Tact Switch

PART NO.

K6-8859D-□□

TOLERANCES ARE

30~125	±0.30
10~30	±0.20
5~10	±0.15
~ 5	±0.10

ANGLE

±2'

UNIT: mm

SCALE: 1:1

PROJ:

DRAWING NO.

—

SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.