








PCB Layout(Pattern Side)



Circuit Diagram



LED colour(LED颜色)	Part No. (料号)
Whiler(白色)	K6-8859D-01
Red(红色)	K6-8859D-02
Blue(蓝色)	K6-8859D-03
Green(普绿)	K6-8859D-04

Typical Specifications

- 1.Rating : DC 12V 50mA
- 2.Operating Force : 250 ± 50 gf
- 3.Contact Resistance : 100mΩMAX
- 4.Life : 100,000 Cycles Min

⑦	LED	—	1	—	Transparent	—
⑥	Keystoke	—	1	PA66	White	—
⑤	Spring	—	1	Keystoke	Ag	—
④	Base	—	1	PA66	Black	—
③	Cover	—	1	PA66	Black	—
②	Terminal	—	6	Phosphor bronze	Ag Plating	—
①	Housing	—	1	Nylon	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	D.J.LV	2017/12/26					
CHECKED				TITLE:	LED Tact Switch		
APPROVALS				PART NO.	K6-8859D-□□		
TOLERANCES ARE	30~ <u>0.15</u>	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.		SHEET 1 OF	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			