







PCB HOLE LAYOUT

NOTE:

1.MATERIAL:

a.HOUSING:THERMOPLASTIC GLASS FIBRE UL94V-0

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING:Ni100u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 30 MILLIOHMS MAX

b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN

c.DIELECTNIC VOLTAGE: 750V AC ONE SEC LEVEL

d.OPERATING TEMPERATURE: -55°C~ +85°C

TOLERANCE		Tolerance:Unless otherwise specified			
LINEAR	ANGLE	3	TERMINAL-2	Mn Steel	Ni-Plated
		2	TERMINAL-1	Mn Steel	Ni-Plated
		1	HOUSING	PBT	BLACK
		NO.	PART NAME	MATERIAL	COLOR/FINISHED

x. ±1
.x ±0.38
.xx ±0.25
.xxx ±0.10

x.° ±5°
.x.° ±2°
.xx.° ±1°

深圳市金航标电子有限公司

www.kinghelm.com.cn

日期DATE

单位UNITS

审核CHECK

BATTERY HDLDER

PART NO.

KH-BS1220-4

0755-28190160

比例SCALE

制图DRAW

设计DESIGN

TITLE:

两PIN电池座卧式 (BS-1220-4)

1/1