






CIRCUIT DIAGRAM

Model No.	1	2	3
PIN	ø1.65	ø2.0	ø2.5

Rating:2.0A 30V DC
Contact Resistance:100 mΩ Max.
Operating temperature:-20℃~70℃
Operating force:3-20N
Operating Life:5,000cycles

④	Metal nut	—	1	Brass	Sn Plating	—
③	Copper sleeve	—	1	Brass	Sn Plating	—
②	Terminal	—	2	Brass	Sn Plating	—
①	Housing	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE										
DRAWN		LIUCAN		2023.6.13									
CHECKED					TITLE:		DC JACKES						
APPROVALS					PART NO.		DC-196						
TOLERANCES ARE			30~以上		±0.30	ANGLE		UNIT: mm		SCALE: 1:1		PROJ: 	
			10~30		±0.20								
			5~10		±0.15								
			~ 5		±0.10								
					±2'	DRAWING NO.				SHEET 1 OF			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			