





RECOMMENDED P.C.B. LAYOUT (T:1.00mm)
TOLERANCE UNSPECIFIED ±0.05mm

NOTE:

- 1.MATERIAL SPECIFICATION:
 - 1.HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC.
 - 2.CONTACTS: COPPER ALLOY
 - 3.MID PLATE: STAINLESS STEEL
 - 4.SHELL: STAINLESS STEEL
- 2.PLATING SPECIFICATION:
 - 2-1.CONTACTS:
 - Ni 50u" MIN. UNDER PLATED OVER ALL.
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.
 - (GOLD PLATING THICKNESS FOLLOW THE P/N)
 - GOLD FLASH PLATING ON SOLDER AREA
 - 2-2.FRONT SHELL:
 - Ni 50u" MIN. UNDER PLATED OVER ALL.
- 3.MECHANICAL PERFORMANCE,
 - 3-1.INSERTION FORCE: 0.5~2.0kgf.
 - 3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.
 - 3-3.DURABILITY: 10000 CYCLES.
- 4.ELECTRICAL PERFORMANCE,
 - 4-1.INSULATION RESISTANCE: 100MΩ MIN
 - 4-2.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
5. ENVIRONMENTAL PERFORMANCE:
 - OPERATING TEMPERATURE: -40°C~+85°C.
- 6.IR REFLOW:
 - THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B7	DN2
A6	DP1	B6	DP2
A7	DN1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

APPROVALS		DATE																			
DRAWN	LIUCAN	2022.06.08					TITLE:	USB CONNECTOR													
CHECKED				PART NO.	TYPE-C-31-D-17																
APPROVALS				TOLERANCES ARE	<table border="1"> <tbody> <tr> <td>30~以上</td> <td>±0.30</td> <td rowspan="2">ANGLE</td> <td rowspan="2">UNIT: mm</td> <td rowspan="2">SCALE: 1:1</td> <td rowspan="2">PROJ: </td> </tr> <tr> <td>10~30</td> <td>±0.20</td> </tr> <tr> <td>5~10</td> <td>±0.15</td> <td rowspan="2">±2'</td> <td rowspan="2">DRAWING NO.</td> <td rowspan="2"></td> <td rowspan="2">SHEET 1 OF 1</td> </tr> <tr> <td>~ 5</td> <td>±0.10</td> </tr> </tbody> </table>	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	10~30	±0.20	5~10	±0.15	±2'	DRAWING NO.		SHEET 1 OF 1	~ 5	±0.10
30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 																
10~30	±0.20																				
5~10	±0.15	±2'	DRAWING NO.		SHEET 1 OF 1																
~ 5	±0.10																				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			