



产品编号：1200651108

系列号：120065

Product Category：Circular Industrial Cordsets

Product Description：Micro-Change (M12) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length

状态：Active

工程编号：803000K05M020

文件和资源

图纸

图纸 1200651108_sd.pdf

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

欧盟 RoHS 合格证书

产品详情

常规

状态	活动
类别	Circular Industrial Cordsets
系列	120065
说明	Micro-Change (M12) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length
IP 等级	IP67
产品系列	Brad Micro-Change (M12) Connectors
产品名称	Micro-Change (M12)
地区	America
类型	Single Ended
UPC	78678853301

机构

CSA	LR6837
UL	E152210

电气

每触点最大电流	4.0A
电压 - 最大	250V AC/DC

物理

电缆直径	5.00mm (.197")
电缆长度	2.0m (6.56'))
电缆护套颜色	黄色
连接器 A 端	Micro-Change (M12)
连接器 B 端	Pigtail
耦合方式	Threaded
性别	Female-Pigtail
键槽	Single
LED 指示器	否
材料—电缆护套	TPE

材料—连接器体	TPE
材料 - 触头	Brass
材料—连接螺母	Nickel-plated Brass
材料—O形圈	Fluoro-elastomer
材料 - 接合部位电镀	金牌
净重	29.029/g
方向	Straight to Pigtail
极柱	3
运行温度范围	-25° to +85° C
导线/电缆型号	PLTC/ITC
线径规格 (AWG)	22