







SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating: 7A, AC/DC
- Withstanding Voltage:1, 500V AC/minute
- Insulation resistance:1, 000MΩ min
- Temperature range: -40℃ to+105℃
- Contact resistance:20mΩ max

HOUSING

- Part No:CS-5001-05
- Part No:2-14
- Material:PA66 UL94V-2 本色
- Q'TY: 500/1000 pcs/Bag

Poles	PART NO	D I M E N S I O N (mm)		Poles	PART NO	D I M E N S I O N (mm)	
		A	B			A	B
2	CS-5001-02	3.96	8.92	9	CS-5001-09	31.68	36.64
3	CS-5001-03	7.92	12.88	10	CS-5001-10	35.64	40.60
4	CS-5001-04	11.88	16.84	11	CS-5001-11	39.60	44.56
5	CS-5001-05	15.84	20.80	12	CS-5001-12	43.56	48.52
6	CS-5001-06	19.80	24.76	13	CS-5001-13	47.52	52.48
7	CS-5001-07	23.76	28.72	14	CS-5001-14	51.48	56.44
8	CS-5001-08	27.72	32.68				

SECTION : A-A

E										本公司保留法律追究的权利.									
有,未經書面許可不准擅自傳閱、复制和修改.										E									
由巧盛企業有限公司所有,未經書面許可不准擅自傳閱、复制和修改.										E									
本圖紙知識產權及版權										E									
類別										Housing									
品 名										CS-5001-05									
X.										±0.50									
版 本										A/0									
設計										李文暢									
X. X										±0.40									
制定部門										工程課									
繪 制										李文暢									
X. XX										±0.30									
工程圖號										CST-A05001									
審 核										姚 培 柱									
X. XXX										±0.20									
制定日期										2018-06-08									
核 准										韋 棟 釋									
X. XXXX										±0.10									
材料										顏色									
單位										mm									
1:1										1									
修改內容										修改日期									
2										1									
3										2									
CST										SHENZHEN YONGFENG YING ENTERPRISE LTD.									
深圳 永丰盈电子有限公司										CST									