


技术特性/Specifications:

额定电压 Rated voltage: 250V AC, DC  
额定电流 Rated current: 3A AC, DC  
接触电阻 Contact resistance: 20mΩ max  
绝缘电阻 Insulation resistance: 1000MΩ min  
耐压 Withstand voltage: 1000V AC/minute  
环境温度 Ambient temperature: -40℃~+105℃  
适用线规 Wire range: AWG#32~#28



A

B

C

D

E

F

A

B

C

D

E

F

12345678

12345678

12345678


12345678

12345678


12345678

12345678

12345678





SECTION A-A




NORES:

- 1、Rated voltage: 250V AC.DC
- 2、Rated current: 3A AC DC
- 3、Contact resistance: ≤20 mΩ
- 4、Insulation resistance: ≥1000 mΩ
- 5、Withstand voltage: 1000V AC/minute
- 6、Ambient temprature:-25℃~85℃
- 7、Materials:LCP UL94V-0
- 8、Matched RoHS criteria



|    |    |     |     |    |         |
|----|----|-----|-----|----|---------|
| 3  | ③  | 基座  | LCP | 1  | UL94-V0 |
| 2  | ②  | 焊片  | 黄铜  | 2  | 镀锡      |
| 1  | ①  | 接触件 | 黄铜  | N* | 镀锡      |
| 序号 | 图号 | 名称  | 材料  | 数量 | 附件      |

| Circuits | Product name | Dimension mm |       | Circuits | Product name | Dimension mm |       |
|----------|--------------|--------------|-------|----------|--------------|--------------|-------|
|          |              | A            | B     |          |              | A            | B     |
| 2        | DL25018-2AB  | 2.50         | 10.00 | 10       | DL25018-10AB | 22.50        | 30.00 |
| 3        | DL25018-3AB  | 5.00         | 12.50 | 11       | DL25018-11AB | 25.00        | 32.50 |
| 4        | DL25018-4AB  | 7.50         | 15.00 | 12       | DL25018-12AB | 27.50        | 35.00 |
| 5        | DL25018-5AB  | 10.00        | 17.50 | 13       | DL25018-13AB | 30.00        | 37.50 |
| 6        | DL25018-6AB  | 12.50        | 20.00 | 14       | DL25018-14AB | 32.50        | 40.00 |
| 7        | DL25018-7AB  | 15.00        | 22.50 | 15       | DL25018-15AB | 35.00        | 42.50 |
| 8        | DL25018-8AB  | 17.50        | 25.00 | -        | -            | -            | -     |
| 9        | DL25018-9AB  | 20.00        | 27.50 | 20       | DL25018-20AB | 47.50        | 55.00 |





PCB LAYOUT





| GENERAL TOLERANCES (UNLESS SPECIFIED) |               |                   |               | ZHE JIANG DELI CONNECTORS CO .,LTD           |  |           |  |
|---------------------------------------|---------------|-------------------|---------------|----------------------------------------------|--|-----------|--|
| .X: ± 0.25                            | X° : ± 3.0°   | PRODUCT NAME:     |               | TITLE: 2.50 mm Pitch Wire To Board SMT Wafer |  |           |  |
| .XX: ± 0.15                           | .X° : ± 2.0°  | DL25018-AB        |               | PART NO:                                     |  |           |  |
| .XXX: ± 0.01                          | .XX° : ± 1.0° | DR:Chen Quan Long | DATE:18/03/03 | SCALE: N/A                                   |  |           |  |
| FINISH:                               |               | CHKD:Wu Hui       | DATE:18/03/03 | UNITS: mm                                    |  | PAGE: 1/1 |  |
| DRAWING NO:                           |               | APPD:Ren An De    | DATE:18/03/03 | REV.: B                                      |  |           |  |

A  
B  
C  
D  
E  
F

| 1    | 2 | 3                    | 4 | 5 | 6 | 7    | 8    |
|------|---|----------------------|---|---|---|------|------|
| REV. |   | REVISION DESCRIPTION |   |   |   | DATE | APPD |
|      |   |                      |   |   |   |      |      |



Circuit No.1



- NORES:
- 1、Rated voltage: 250V AC.DC
  - 2、Rated current: 3A AC DC
  - 3、Contact resistance:  $\leq 20\text{ m}\Omega$
  - 4、Insulation resistance:  $\geq 1000\text{ m}\Omega$
  - 5、Withstand voltage: 1000V AC/minute
  - 6、Ambient temprature:  $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$
  - 7、Materials:LCP UL94V-0
  - 8、Matched RoHS criteria

|    |    |     |     |    |         |
|----|----|-----|-----|----|---------|
| 3  | ③  | 基座  | LCP | 1  | UL94-V0 |
| 2  | ②  | 焊片  | 黄铜  | 2  | 镀锡      |
| 1  | ①  | 接触件 | 黄铜  | N* | 镀锡      |
| 序号 | 图号 | 名称  | 材料  | 数量 | 附件      |





| Circuits | Product name | Dimension mm |       | Circuits | Product name  | Dimension mm |       |
|----------|--------------|--------------|-------|----------|---------------|--------------|-------|
|          |              | A            | B     |          |               | A            | B     |
| 2        | DL25018-2AWB | 2.50         | 10.00 | 10       | DL25018-10AWB | 22.50        | 30.00 |
| 3        | DL25018-3AWB | 5.00         | 12.50 | 11       | DL25018-11AWB | 25.00        | 32.50 |
| 4        | DL25018-4AWB | 7.50         | 15.00 | 12       | DL25018-12AWB | 27.50        | 35.00 |
| 5        | DL25018-5AWB | 10.00        | 17.50 | 13       | DL25018-13AWB | 30.00        | 37.50 |
| 6        | DL25018-6AWB | 12.50        | 20.00 | 14       | DL25018-14AWB | 32.50        | 40.00 |
| 7        | DL25018-7AWB | 15.00        | 22.50 | 15       | DL25018-15AWB | 35.00        | 42.50 |
| 8        | DL25018-8AWB | 17.50        | 25.00 | -        | -             | -            | -     |
| 9        | DL25018-9AWB | 20.00        | 27.50 | 20       | DL25018-20AWB | 47.50        | 55.00 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) |              |                   |               | ZHE JIANG DELI CONNECTORS CO.,LTD            |  |         |  |
|---------------------------------------|--------------|-------------------|---------------|----------------------------------------------|--|---------|--|
| .X: ± 0.25                            | X°: ± 3.0°   | PRODUCT NAME:     |               | TITLE: 2.50 mm Pitch Wire To Board SMT Wafer |  |         |  |
| .XX: ± 0.15                           | .X°: ± 2.0°  | DL25018-AWB       |               | PART NO:                                     |  |         |  |
| .XXX: ± 0.01                          | .XX°: ± 1.0° | DR:Chen Quan Long | DATE:23/08/01 | SCALE: N/A                                   |  |         |  |
| FINISH:                               |              | CHKD:Wu Hui       | DATE:23/08/01 | PAGE: 1/1                                    |  |         |  |
| DRAWING NO:                           |              | APPD:Ren An De    | DATE:23/08/01 | UNITS: mm                                    |  | REV.: B |  |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

NOTES

Available in 02 through 20 Circuits.  
Mates with DL25018-Y Series Housing.  
Material : Nylon UL94V-0(2).  
0.6mm round Pin.  
Pin Material : Brass / Tin-Plated.



PCB LAYOUT

| Circuits | Product name | Dimension mm |       | Circuits | Product name | Dimension mm |       |
|----------|--------------|--------------|-------|----------|--------------|--------------|-------|
|          |              | A            | B     |          |              | A            | B     |
| 2        | DL25018-2A   | 2.50         | 7.50  | 10       | DL25018-10A  | 22.50        | 27.50 |
| 3        | DL25018-3A   | 5.00         | 10.00 | 11       | DL25018-11A  | 25.00        | 30.00 |
| 4        | DL25018-4A   | 7.50         | 12.50 | 12       | DL25018-12A  | 27.50        | 32.50 |
| 5        | DL25018-5A   | 10.00        | 15.00 | 13       | DL25018-13A  | 30.00        | 35.00 |
| 6        | DL25018-6A   | 12.50        | 17.50 | 14       | DL25018-14A  | 32.50        | 37.50 |
| 7        | DL25018-7A   | 15.00        | 20.00 | 15       | DL25018-15A  | 35.00        | 40.00 |
| 8        | DL25018-8A   | 17.50        | 22.50 | -        | -            | -            | -     |
| 9        | DL25018-9A   | 20.00        | 25.00 | 20       | DL25018-20A  | 47.50        | 52.50 |

GENERAL TOLERANCES  
(UNLESS SPECIFIED)

|              |               |
|--------------|---------------|
| .X: ± 0.25   | X° : ± 3.0°   |
| .XX: ± 0.15  | .X° : ± 2.0°  |
| .XXX: ± 0.01 | .XX° : ± 1.0° |

FINISH:

DRAWING NO:

CHKD: Wu Hui

APPD: Ren An De

ZHE JIANG DELI CONNECTORS CO.,LTD

PRODUCT NAME:  
DL25018-A

TITLE: 2.50 mm Pitch  
Wire To Board Wafer

DR:Chen Quan Long DATE:20/08/01

CHKD: Wu Hui DATE:20/08/01

APPD:Ren An De DATE:20/08/01

PART NO:  
SCALE: N/A PAGE: 1/1  
UNITS: mm REV.: A

A

B

C

D

E

F

1

2

3

4

5

6





7

8

| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |


NOTES

Available in 02 through 20 Circuits.  
Mates with DL25018-Y Series Housing.  
Material : Nylon UL94V-0(2).  
0.6mm round Pin.  
Pin Material : Brass / Tin-Plated.



P. C. B LATOUT

| Circuits | Product name | Dimension mm |       | Circuits | Product name | Dimension mm |       |
|----------|--------------|--------------|-------|----------|--------------|--------------|-------|
|          |              | A            | B     |          |              | A            | B     |
| 2        | DL25018-2AS  | 2.50         | 7.50  | 10       | DL25018-10AS | 22.50        | 27.50 |
| 3        | DL25018-3AS  | 5.00         | 10.00 | 11       | DL25018-11AS | 25.00        | 30.00 |
| 4        | DL25018-4AS  | 7.50         | 12.50 | 12       | DL25018-12AS | 27.50        | 32.50 |
| 5        | DL25018-5AS  | 10.00        | 15.00 | 13       | DL25018-13AS | 30.00        | 35.00 |
| 6        | DL25018-6AS  | 12.50        | 17.50 | 14       | DL25018-14AS | 32.50        | 37.50 |
| 7        | DL25018-7AS  | 15.00        | 20.00 | 15       | DL25018-15AS | 35.00        | 40.00 |
| 8        | DL25018-8AS  | 17.50        | 22.50 | -        | -            | -            | -     |
| 9        | DL25018-9AS  | 20.00        | 25.00 | 20       | DL25018-20AS | 47.50        | 52.50 |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |                                                                                       | ZHE JIANG DELI CONNECTORS CO .,LTD |               |                                             |           |
|------------------------------------------|---------------------------------------------------------------------------------------|------------------------------------|---------------|---------------------------------------------|-----------|
| .X: ± 0.25                               | X° : ± 3.0°                                                                           | PRODUCT NAME:<br>DL25018-AS        |               | TITLE: 2.50 mm Pitch<br>Wire To Board Wafer |           |
| .XX: ± 0.15                              | .X° : ± 2.0°                                                                          |                                    |               |                                             |           |
| .XXX: ± 0.01                             | .XX° : ± 1.0°                                                                         | DR: Ke Xian Qiang                  | DATE:09/08/01 | PART NO:                                    |           |
| FINISH:<br>_____                         |  | CHKD: Liu Bing                     | DATE:09/08/01 |                                             |           |
| DRAWING NO:                              |                                                                                       | APPD:Ren An De                     | DATE:09/08/01 | SCALE: N/A                                  | PAGE: 1/1 |
|                                          |                                                                                       |                                    |               | UNITS: mm                                   | REV. : A  |

A

B

C

D

E

F

1

2

3


4

5

6

7

8



| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

NOTES

Available in 02 through 20 Circuits.  
Mates with DL25018-Y Series Housing.  
Material : Nylon UL94V-0(2).  
0.6mm round Pin.  
Pin Material : Brass / Tin-Plated

| Circuits | Product name | Dimension mm |       | Circuits | Product name  | Dimension mm |       |
|----------|--------------|--------------|-------|----------|---------------|--------------|-------|
|          |              | A            | B     |          |               | A            | B     |
| 2        | DL25018-2AWD | 2.50         | 7.50  | 10       | DL25018-10AWD | 22.50        | 27.50 |
| 3        | DL25018-3AWD | 5.00         | 10.00 | 11       | DL25018-11AWD | 25.00        | 30.00 |
| 4        | DL25018-4AWD | 7.50         | 12.50 | 12       | DL25018-12AWD | 27.50        | 32.50 |
| 5        | DL25018-5AWD | 10.00        | 15.00 | 13       | DL25018-13AWD | 30.00        | 35.00 |
| 6        | DL25018-6AWD | 12.50        | 17.50 | 14       | DL25018-14AWD | 32.50        | 37.50 |
| 7        | DL25018-7AWD | 15.00        | 20.00 | 15       | DL25018-15AWD | 35.00        | 40.00 |
| 8        | DL25018-8AWD | 17.50        | 22.50 | -        | -             | -            | -     |
| 9        | DL25018-9AWD | 20.00        | 25.00 | 20       | DL25018-20AWD | 47.50        | 52.50 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) |               |                   |               | ZHE JIANG DELI CONNECTORS CO.,LTD        |  |  |  |
|---------------------------------------|---------------|-------------------|---------------|------------------------------------------|--|--|--|
| .X: ± 0.25                            | X° : ± 3.0°   | PRODUCT NAME:     |               | TITLE: 2.50 mm Pitch Wire To Board Wafer |  |  |  |
| .XX: ± 0.15                           | .X° : ± 2.0°  | DL25018-AWD       |               | PART NO:                                 |  |  |  |
| .XXX: ± 0.01                          | .XX° : ± 1.0° | DR:Chen Quan Long | DATE:20/08/01 | SCALE: N/A PAGE: 1/1                     |  |  |  |
| FINISH:                               |               | CHKD: Wu Hui      | DATE:20/08/01 | UNITS: mm REV.: A                        |  |  |  |
| DRAWING NO:                           |               | APPD:Ren An De    | DATE:20/08/01 |                                          |  |  |  |

PCB LAYOUT

A

B

C

D

E

F

A

B

C

D




E

F

| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

NOTES

Available in 02 through 20 Circuits.  
Mates with DL25018-Y Series Housing.  
Material : Nylon UL94V-0(2).  
0.6mm round Pin.  
Pin Material : Brass / Tin-Plated.







| Circuits | Product name   | Dimension mm |       | Circuits | Product name    | Dimension mm |       |
|----------|----------------|--------------|-------|----------|-----------------|--------------|-------|
|          |                | A            | B     |          |                 | A            | B     |
| 2        | DL25018-2AWD-S | 2.50         | 7.50  | 10       | DL25018-10AWD-S | 22.50        | 27.50 |
| 3        | DL25018-3AWD-S | 5.00         | 10.00 | 11       | DL25018-11AWD-S | 25.00        | 30.00 |
| 4        | DL25018-4AWD-S | 7.50         | 12.50 | 12       | DL25018-12AWD-S | 27.50        | 32.50 |
| 5        | DL25018-5AWD-S | 10.00        | 15.00 | 13       | DL25018-13AWD-S | 30.00        | 35.00 |
| 6        | DL25018-6AWD-S | 12.50        | 17.50 | 14       | DL25018-14AWD-S | 32.50        | 37.50 |
| 7        | DL25018-7AWD-S | 15.00        | 20.00 | 15       | DL25018-15AWD-S | 35.00        | 40.00 |
| 8        | DL25018-8AWD-S | 17.50        | 22.50 | -        | -               | -            | -     |
| 9        | DL25018-9AWD-S | 20.00        | 25.00 | 20       | DL25018-20AWD-S | 47.50        | 52.50 |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |                                                                                       | ZHE JIANG DELI CONNECTORS CO .,LTD |               |                                             |          |
|------------------------------------------|---------------------------------------------------------------------------------------|------------------------------------|---------------|---------------------------------------------|----------|
| .X: ± 0.25                               | X° : ± 3.0°                                                                           | PRODUCT NAME:<br>DL25018-AWD-S     |               | TITLE: 2.50 mm Pitch<br>Wire To Board Wafer |          |
| .XX: ± 0.15                              | .X° : ± 2.0°                                                                          | DR:Chen Quan Long                  | DATE:20/08/01 | PART NO:                                    |          |
| .XXX: ± 0.01                             | .XX° : ± 1.0°                                                                         | CHKD: Wu Hui                       | DATE:20/08/01 | SCALE: N/A      PAGE: 1/1                   |          |
| FINISH:<br>_____                         |  |                                    |               |                                             |          |
| DRAWING NO:                              |                                                                                       | APPD:Ren An De                     | DATE:20/08/01 | UNITS: mm                                   | REV. : A |

A  
B  
C  
D  
E  
F

| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

CIRCUIT NO. 1



NOTES

Available in 02 through 20 Circuits.  
Match with DL25018 series housing  
Material : Nylon UL94V-0(2).  
Accepts DL25018-T Crimp Terminal.

| Circuits | Product name | Dimension mm |       | Circuits | Product name | Dimension mm |       |
|----------|--------------|--------------|-------|----------|--------------|--------------|-------|
|          |              | A            | B     |          |              | A            | B     |
| 2        | DL25018-2Y   | 2.50         | 7.30  | 12       | DL25018-12Y  | 27.50        | 32.30 |
| 3        | DL25018-3Y   | 5.00         | 9.80  | 13       | DL25018-13Y  | 30.00        | 34.80 |
| 4        | DL25018-4Y   | 7.50         | 12.30 | 14       | DL25018-14Y  | 32.50        | 37.30 |
| 5        | DL25018-5Y   | 10.00        | 14.80 | 15       | DL25018-15Y  | 35.00        | 39.80 |
| 6        | DL25018-6Y   | 12.50        | 17.30 | 16       | DL25018-16Y  | 37.50        | 42.30 |
| 7        | DL25018-7Y   | 15.00        | 19.80 | 17       | DL25018-17Y  | 40.00        | 44.80 |
| 8        | DL25018-8Y   | 17.50        | 22.30 | 18       | DL25018-18Y  | 42.50        | 47.30 |
| 9        | DL25018-9Y   | 20.00        | 24.80 | 19       | DL25018-19Y  | 45.00        | 47.30 |
| 10       | DL25018-10Y  | 22.50        | 27.30 | 20       | DL25018-20Y  | 47.50        | 52.30 |
| 11       | DL25018-11Y  | 25.00        | 29.80 |          |              |              |       |




| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |                                                                                       | ZHE JIANG DELI CONNECTORS CO ., LTD |               |                                 |           |
|------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------|---------------|---------------------------------|-----------|
| .X: ± 0.25                               | X° : ± 3.0°                                                                           | PRODUCT NAME:<br>DL25018-Y          |               | TITLE:<br>2.50 mm Pitch Housing |           |
| .XX: ± 0.15                              | .X° : ± 2.0°                                                                          |                                     |               |                                 |           |
| .XXX: ± 0.01                             | .XX° : ± 1.0°                                                                         | DR:Chen Quan Long                   | DATE:20/08/01 | PART NO:                        |           |
| FINISH:<br>_____                         |  | CHKD: Wu Hui                        | DATE:20/08/01 |                                 |           |
| DRAWING NO:                              |                                                                                       | APPD:Ren An De                      | DATE:20/08/01 | SCALE: N/A                      | PAGE: 1/1 |
|                                          |                                                                                       |                                     |               | UNITS: mm                       | REV. : A  |

A  
B  
C  
D  
E  
F

| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

## NORES:

1. Rated voltage: 250V AC.DC
2. Rated current: 3A AC DC
3. Contact resistance:  $\leq 20 \text{ m}\Omega$
4. Insulation resistance:  $\geq 500 \text{ m}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temprature:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
7. Materials: Nylon UL94V-0 (2)
8. Matched RoHS criteria



安装尺寸图

| Circuits | Product name | Dimension mm |       |       |       |       | Circuits | Product name | Dimension mm |       |       |       |       |
|----------|--------------|--------------|-------|-------|-------|-------|----------|--------------|--------------|-------|-------|-------|-------|
|          |              | A            | B     | C     | D     | E     |          |              | A            | B     | C     | D     | E     |
| 2        | DL25018-2R   | 2.50         | 7.50  | 5.90  | 7.90  | 11.20 | 10       | DL25018-10R  | 22.50        | 27.50 | 25.90 | 27.90 | 31.20 |
| 3        | DL25018-3R   | 5.00         | 10.00 | 8.40  | 10.40 | 13.70 | 11       | DL25018-11R  | 25.00        | 30.00 | 28.40 | 30.40 | 33.70 |
| 4        | DL25018-4R   | 7.50         | 12.50 | 10.90 | 12.90 | 16.20 | 12       | DL25018-12R  | 27.50        | 32.50 | 30.90 | 32.90 | 36.20 |
| 5        | DL25018-5R   | 10.00        | 15.00 | 13.40 | 15.40 | 18.70 | 13       | DL25018-13R  | 30.00        | 35.00 | 33.40 | 35.40 | 38.70 |
| 6        | DL25018-6R   | 12.50        | 17.50 | 15.90 | 17.90 | 21.20 | 14       | DL25018-14R  | 32.50        | 37.50 | 35.90 | 37.90 | 41.20 |
| 7        | DL25018-7R   | 15.00        | 20.00 | 18.40 | 20.40 | 23.70 | 15       | DL25018-15R  | 35.00        | 40.00 | 38.40 | 40.40 | 43.70 |
| 8        | DL25018-8R   | 17.50        | 22.50 | 20.90 | 22.90 | 26.20 | -        | -            | -            | -     | -     | -     | -     |
| 9        | DL25018-9R   | 20.00        | 25.00 | 23.40 | 25.40 | 28.70 | 20       | DL25018-20R  | 47.50        | 52.50 | 50.90 | 52.90 | 56.20 |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |              |                                   |                | ZHE JIANG DELI CONNECTORS CO.,LTD            |  |           |  |
|------------------------------------------|--------------|-----------------------------------|----------------|----------------------------------------------|--|-----------|--|
| .X: ± 0.25                               | X°: ± 3.0°   | PRODUCT NAME:<br><b>DL25018-R</b> |                | TITLE: 2.50 mm Pitch<br>Wire To Wire Housing |  |           |  |
| .XX: ± 0.15                              | .X°: ± 2.0°  | DR: Yuan Jun Rong                 | DATE: 21/12/30 | PART NO:                                     |  |           |  |
| .XXX: ± 0.01                             | .XX°: ± 1.0° | CHKD: Wu Hui                      | DATE: 21/12/30 | SCALE: N/A                                   |  | PAGE: 1/1 |  |
| FINISH:                                  |              | APPD: Ren An De                   | DATE: 21/12/30 | UNITS: mm                                    |  | REV.: A   |  |
| DRAWING NO:                              |              |                                   |                |                                              |  |           |  |

A

B

C

D

E

F

A

B

C


D

E


F

| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

- NORES:**
- 1. Rated voltage: 250V AC.DC
  - 2. Rated current: 3A AC DC
  - 3. Contact resistance:  $\leq 20\text{ m}\Omega$
  - 4. Insulation resistance:  $\geq 500\text{ m}\Omega$
  - 5. Withstand voltage: 1500V AC/minute
  - 6. Ambient temprature:  $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$
  - 7. Materials: Nylon UL94V-0(2)
  - 8. Matched RoHS criteria




安装尺寸图



| Circuits | Product name | Dimension mm |       |       |       |       | Circuits | Product name | Dimension mm |       |       |       |       |
|----------|--------------|--------------|-------|-------|-------|-------|----------|--------------|--------------|-------|-------|-------|-------|
|          |              | A            | B     | C     | D     | E     |          |              | A            | B     | C     | D     | E     |
| 2        | DL25018-2RF  | 2.50         | 7.50  | 5.90  | 7.90  | 11.20 | 10       | DL25018-10RF | 22.50        | 27.50 | 25.90 | 27.90 | 31.20 |
| 3        | DL25018-3RF  | 5.00         | 10.00 | 8.40  | 10.40 | 13.70 | 11       | DL25018-11RF | 25.00        | 30.00 | 28.40 | 30.40 | 33.70 |
| 4        | DL25018-4RF  | 7.50         | 12.50 | 10.90 | 12.90 | 16.20 | 12       | DL25018-12RF | 27.50        | 32.50 | 30.90 | 32.90 | 36.20 |
| 5        | DL25018-5RF  | 10.00        | 15.00 | 13.40 | 15.40 | 18.70 | 13       | DL25018-13RF | 30.00        | 35.00 | 33.40 | 35.40 | 38.70 |
| 6        | DL25018-6RF  | 12.50        | 17.50 | 15.90 | 17.90 | 21.20 | 14       | DL25018-14RF | 32.50        | 37.50 | 35.90 | 37.90 | 41.20 |
| 7        | DL25018-7RF  | 15.00        | 20.00 | 18.40 | 20.40 | 23.70 | 15       | DL25018-15RF | 35.00        | 40.00 | 38.40 | 40.40 | 43.70 |
| 8        | DL25018-8RF  | 17.50        | 22.50 | 20.90 | 22.90 | 26.20 | -        | -            | -            | -     | -     | -     | -     |
| 9        | DL25018-9RF  | 20.00        | 25.00 | 23.40 | 25.40 | 28.70 | 20       | DL25018-20RF | 47.50        | 52.50 | 50.90 | 52.90 | 56.20 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) |              |                             |                | ZHE JIANG DELI CONNECTORS CO., LTD           |  |           |  |
|---------------------------------------|--------------|-----------------------------|----------------|----------------------------------------------|--|-----------|--|
| .X: ± 0.25                            | X°: ± 3.0°   | PRODUCT NAME:<br>DL25018-RF |                | TITLE: 2.50 mm Pitch<br>Wire To Wire Housing |  |           |  |
| .XX: ± 0.15                           | .X°: ± 2.0°  | DR: Yuan Jun Rong           | DATE: 21/12/30 | PART NO:                                     |  |           |  |
| .XXX: ± 0.01                          | .XX°: ± 1.0° | CHKD: Wu Hui                | DATE: 21/12/30 | SCALE: N/A                                   |  | PAGE: 1/1 |  |
| FINISH:                               |              | APPD: Ren An De             | DATE: 21/12/30 | UNITS: mm                                    |  | REV.: A   |  |
| DRAWING NO:                           |              |                             |                |                                              |  |           |  |



| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |


NOTES

Available in 02 through 20 Circuits.

Match with DL25018-Y series housing

Material : Nylon UL94V-0(2).

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |                                                                                       | ZHE JIANG DELI CONNECTORS CO ., LTD |               |                                 |           |
|------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------|---------------|---------------------------------|-----------|
| .X: ± 0.25                               | X° : ± 3.0°                                                                           | PRODUCT NAME:<br>DL25018-S          |               | TITLE:<br>2.50 mm Pitch Housing |           |
| .XX: ± 0.15                              | .X° : ± 2.0°                                                                          | DR:Yuan Jun Rong                    | DATE:20/08/01 | PART NO:                        |           |
| .XXX: ± 0.01                             | .XX° : ± 1.0°                                                                         |                                     |               |                                 |           |
| FINISH:<br>_____                         |  | CHKD: Wu Hui                        | DATE:20/08/01 | SCALE: N/A                      | PAGE: 1/1 |
| DRAWING NO:                              |                                                                                       | APPD:Ren An De                      | DATE:20/08/01 | UNITS: mm                       | REV. : A  |



| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

NOTES

Available in 02 through 20 Circuits.


Mates with DL25018-R/DL25034-RK/  
DL25035/DL25045 Series Housing.

Material : Nylon UL94-V0(2).

Green Material RoHS Compliant.

| Circuits | Product name | Dimension mm |      | Circuits | Product name | Dimension mm |      |
|----------|--------------|--------------|------|----------|--------------|--------------|------|
|          |              | A            | B    |          |              | A            | B    |
| 2        | DL25018-2RS  | 2.50         | 4.4  | 10       | DL25018-10RS | 22.50        | 24.4 |
| 3        | DL25018-3RS  | 5.00         | 6.9  | 11       | DL25018-11RS | 25.00        | 26.9 |
| 4        | DL25018-4RS  | 7.50         | 9.4  | 12       | DL25018-12RS | 27.50        | 29.4 |
| 5        | DL25018-5RS  | 10.00        | 11.9 | 13       | DL25018-13RS | 30.00        | 31.9 |
| 6        | DL25018-6RS  | 12.50        | 14.4 | 14       | DL25018-14RS | 32.50        | 34.4 |
| 7        | DL25018-7RS  | 15.00        | 16.9 | 15       | DL25018-15RS | 35.00        | 36.9 |
| 8        | DL25018-8RS  | 17.50        | 19.4 | -        | -            | -            | -    |
| 9        | DL25018-9RS  | 20.00        | 21.9 | 20       | DL25018-RS   | 47.50        | 49.4 |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |               | ZHE JIANG DELI CONNECTORS CO.,LTD |               |                                     |          |
|------------------------------------------|---------------|-----------------------------------|---------------|-------------------------------------|----------|
| .X: ± 0.25                               | X° : ± 3.0°   | PRODUCT NAME:<br>DL25018-RS       |               | TITLE: 2.5 mm Pitch<br>Wire To Wire |          |
| .XX: ± 0.15                              | .X° : ± 2.0°  | DR:Chen Quan Long                 | DATE:21/05/01 | PART NO:                            |          |
| .XXX: ± 0.01                             | .XX° : ± 1.0° |                                   |               | SCALE: N/A                          |          |
| FINISH:                                  |               | CHKD: Wu Hui                      | DATE:21/05/01 | PAGE: 1/1                           |          |
| DRAWING NO:                              |               | APPD:Ren An De                    | DATE:21/05/01 | UNITS: mm                           | REV. : A |



| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

技术特性/Specifications:  
额定电压Rated voltage :250V AC.DC.  
额定电流Rated current :3A AC.DC.  
接触电阻Contact resistance:20MΩ MAX  
绝缘电阻Insulation resistance: 1000 MΩ MIN  
耐压Withstand voltage:1000V AC/minute  
环境温度Ambient temperature: -40℃~+105℃  
适用线规 Wire range: AWG#28~#20  
材料/Materials:  
端子Terminal: 磷青铜Phosphor bronze ,  
镀锡Tin plated

| Product name | Dimension (mm) |     |     |     | Applicable wire | Insulation O. D. (mm) |
|--------------|----------------|-----|-----|-----|-----------------|-----------------------|
|              | A1             | B1  | A2  | B2  |                 |                       |
| DL25018-T    | 2.9            | 3.0 | 1.9 | 1.6 | AWG#28-22       | 1.9mm Max             |
| DL25018-T-G  | 2.9            | 3.0 | 2.3 | 2.1 | AWG#24-20       | 1.9mm Max             |

| GENERAL TOLERANCES (UNLESS SPECIFIED) |               |                         |               | ZHE JIANG DELI CONNECTORS CO .,LTD  |  |         |  |
|---------------------------------------|---------------|-------------------------|---------------|-------------------------------------|--|---------|--|
| .X: ± 0.25                            | X° : ± 3.0°   | PRODUCT NAME: DL25018-T |               | TITLE: 2.50 mm Pitch Crimp Terminal |  |         |  |
| .XX: ± 0.15                           | .X° : ± 2.0°  | DR: Yuan Jun Rong       | DATE:21/12/30 | PART NO:                            |  |         |  |
| .XXX: ± 0.01                          | .XX° : ± 1.0° |                         |               | SCALE: N/A                          |  |         |  |
| FINISH:                               |               | CHKD: Wu Hui            | DATE:21/12/30 | PAGE: 1/1                           |  |         |  |
| DRAWING NO:                           |               | APPD:Ren An De          | DATE:21/12/30 | UNITS: mm                           |  | REV.: A |  |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|------|----------------------|------|------|
|      |                      |      |      |

技术特性/Specifications:  
额定电压Rated voltage :250V AC.DC.  
额定电流Rated current :3A AC.DC.  
接触电阻Contact resistance:20MΩ MAX  
绝缘电阻Insulation resistance: 500 MΩ MIN  
耐压Withstand voltage:1500V AC/minute  
环境温度Ambient temperature: -40℃~+105℃  
适用线规 Wire range: AWG#28~#20  
材料/Materials:  
端子Terminal: 磷青铜Phosphor bronze ,  
镀锡Tin plated

| Product name | Dimension (mm) |     |     |     | Applicable wire | Insulation O.D. (mm) |
|--------------|----------------|-----|-----|-----|-----------------|----------------------|
|              | A1             | B1  | A2  | B2  |                 |                      |
| DL25018-RT   | 2.9            | 2.9 | 1.9 | 1.5 | AWG#28-22       | 1.9mm Max            |
| DL25018-RT-G | 2.9            | 2.9 | 2.2 | 2.1 | AWG#24-20       | 1.9mm Max            |

| GENERAL TOLERANCES (UNLESS SPECIFIED) |              | ZHE JIANG DELI CONNECTORS CO.,LTD |               |                                        |           |
|---------------------------------------|--------------|-----------------------------------|---------------|----------------------------------------|-----------|
| .X: ± 0.25                            | X°: ± 3.0°   | PRODUCT NAME:                     |               | TITLE:                                 |           |
| .XX: ± 0.15                           | .X°: ± 2.0°  | DL25018-RT                        |               | 2.50 mm Pitch<br>Wire To Wire Terminal |           |
| .XXX: ± 0.01                          | .XX°: ± 1.0° | DR:Yuan Jun Rong                  | DATE:21/12/30 | PART NO:                               |           |
| FINISH:                               |              | CHKD:Wu Hui                       | DATE:21/12/30 | SCALE: N/A                             | PAGE: 1/1 |
| DRAWING NO:                           |              | APPD:Ren An De                    | DATE:21/12/30 | UNITS: mm                              | REV.: A   |


| REV. | REVISION | DESCRIPTION | DATE | APPD |
|------|----------|-------------|------|------|
|      |          |             |      |      |

NOTES

Available in 02 through 20 Circuits.  
Mates with DL25018-Y Series Housing.  
Material : Nylon UL94V-0.  
0.60mm Square Pin.  
Pin Material : Brass / Tin-Plated.

| Circuits | Product name | Dimension mm |       |       | Circuits | Product name | Dimension mm |       |       |
|----------|--------------|--------------|-------|-------|----------|--------------|--------------|-------|-------|
|          |              | A            | B     | C     |          |              | A            | B     | C     |
| 2        | XAH-2A       | 2.50         | 7.50  | 5.90  | 10       | XAH-10A      | 22.50        | 27.50 | 25.90 |
| 3        | XAH-3A       | 5.00         | 10.00 | 8.40  | 11       | XAH-11A      | 25.00        | 30.00 | 28.40 |
| 4        | XAH-4A       | 7.50         | 12.50 | 10.90 | 12       | XAH-12A      | 27.50        | 32.50 | 30.90 |
| 5        | XAH-5A       | 10.00        | 15.00 | 13.40 | 13       | XAH-13A      | 30.00        | 35.00 | 33.40 |
| 6        | XAH-6A       | 12.50        | 17.50 | 15.90 | 14       | XAH-14A      | 32.50        | 37.50 | 35.90 |
| 7        | XAH-7A       | 15.00        | 20.00 | 18.40 | 15       | XAH-15A      | 35.00        | 40.00 | 38.40 |
| 8        | XAH-8A       | 17.50        | 22.50 | 20.90 | -        | -            | -            | -     | -     |
| 9        | XAH-9A       | 20.00        | 25.00 | 23.40 | 20       | XAH-20A      | 47.50        | 52.50 | 50.90 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) |              |                                          |                | ZHE JIANG DELI CONNECTORS CO., LTD             |  |           |  |
|---------------------------------------|--------------|------------------------------------------|----------------|------------------------------------------------|--|-----------|--|
| .X: ± 0.25                            | X°: ± 3.0°   | PRODUCT NAME:<br><b>DL25035 (XAH) -A</b> |                | TITLE:<br>2.50 mm Pitch<br>Wire To Board Wafer |  |           |  |
| .XX: ± 0.15                           | .X°: ± 2.0°  | DR: Yuan Jun Rong                        | DATE: 19/07/20 | PART NO:                                       |  |           |  |
| .XXX: ± 0.01                          | .XX°: ± 1.0° | CHKD: Wu Hui                             | DATE: 19/07/20 | SCALE: N/A                                     |  | PAGE: 1/1 |  |
| DRAWING NO:                           |              | APPD: Ren An De                          | DATE: 19/07/20 | UNITS: mm                                      |  | REV.: A   |  |







A  
B  
C  
D  
E  
F

| 7    |                      | 8    |      |
|------|----------------------|------|------|
| REV. | REVISION DESCRIPTION | DATE | APPD |
|      |                      |      |      |

# NOTES

Available in 02 through 20 Circuits.  
Mates with DL25018-Y Series Housing.  
Material : Nylon UL94V-0.  
0.60mm Square Pin.  
Pin Material : Brass / Tin-Plated.



| Circuits | Product name | Dimension mm |       |       | Circuits | Product name | Dimension mm |       |       |
|----------|--------------|--------------|-------|-------|----------|--------------|--------------|-------|-------|
|          |              | A            | B     | C     |          |              | A            | B     | C     |
| 2        | XAH-2AS      | 2.50         | 7.50  | 5.90  | 10       | XAH-10AS     | 22.50        | 27.50 | 25.90 |
| 3        | XAH-3AS      | 5.00         | 10.00 | 8.40  | 11       | XAH-11AS     | 25.00        | 30.00 | 28.40 |
| 4        | XAH-4AS      | 7.50         | 12.50 | 10.90 | 12       | XAH-12AS     | 27.50        | 32.50 | 30.90 |
| 5        | XAH-5AS      | 10.00        | 15.00 | 13.40 | 13       | XAH-13AS     | 30.00        | 35.00 | 33.40 |
| 6        | XAH-6AS      | 12.50        | 17.50 | 15.90 | 14       | XAH-14AS     | 32.50        | 37.50 | 35.90 |
| 7        | XAH-7AS      | 15.00        | 20.00 | 18.40 | 15       | XAH-15AS     | 35.00        | 40.00 | 38.40 |
| 8        | XAH-8AS      | 17.50        | 22.50 | 20.90 | -        | -            | -            | -     | -     |
| 9        | XAH-9AS      | 20.00        | 25.00 | 23.40 | 20       | XAH-20AS     | 47.50        | 52.50 | 50.90 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) |               | ZHE JIANG DELI CONNECTORS CO., LTD |                                          |
|---------------------------------------|---------------|------------------------------------|------------------------------------------|
| .X: ± 0.25                            | X° : ± 3.0°   | PRODUCT NAME: DL25035 (XAH)-AS     | TITLE: 2.50 mm Pitch Wire To Board Wafer |
| .XX: ± 0.15                           | .X° : ± 2.0°  | DR: Yuan Jun Rong                  | DATE: 19/07/20                           |
| .XXX: ± 0.01                          | .XX° : ± 1.0° | CHKD: Wu Hui                       | DATE: 19/07/20                           |
| FINISH: _____                         |               | APPD: Ren An De                    | DATE: 19/07/20                           |
| DRAWING NO: _____                     |               |                                    |                                          |

A




B

C

D

E

F



## NOTES

Available in 02 through 20 Circuits.  
Match with DL25018 or DL25035 series housing  
Material : Nylon UL94V-0(2).  
Accepts DL25035-T Crimp Terminal.

| Circuits | Product name | Dimension mm |       | Circuits | Product name | Dimension mm |       |
|----------|--------------|--------------|-------|----------|--------------|--------------|-------|
|          |              | A            | B     |          |              | A            | B     |
| 2        | XAH-2Y       | 2.50         | 7.30  | 12       | XAH-12Y      | 27.50        | 32.30 |
| 3        | XAH-3Y       | 5.00         | 9.80  | 13       | XAH-13Y      | 30.00        | 34.80 |
| 4        | XAH-4Y       | 7.50         | 12.30 | 14       | XAH-14Y      | 32.50        | 37.30 |
| 5        | XAH-5Y       | 10.00        | 14.80 | 15       | XAH-15Y      | 35.00        | 39.80 |
| 6        | XAH-6Y       | 12.50        | 17.30 | 16       | XAH-16Y      | 37.50        | 42.30 |
| 7        | XAH-7Y       | 15.00        | 19.80 | 17       | XAH-17Y      | 40.00        | 44.80 |
| 8        | XAH-8Y       | 17.50        | 22.30 | 18       | XAH-18Y      | 42.50        | 47.30 |
| 9        | XAH-9Y       | 20.00        | 24.80 | 19       | XAH-19Y      | 45.00        | 47.30 |
| 10       | XAH-10Y      | 22.50        | 27.30 | 20       | XAH-20Y      | 47.50        | 52.30 |
| 11       | XAH-11Y      | 25.00        | 29.80 |          |              |              |       |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |               |                                   |             | ZHE JIANG DELI CONNECTORS CO ., LTD |               |            |           |
|------------------------------------------|---------------|-----------------------------------|-------------|-------------------------------------|---------------|------------|-----------|
| .X: ± 0.25                               | X° : ± 3.0°   | PRODUCT NAME:<br>DL25035 (XAH) -Y |             | TITLE:<br>2.50 mm Pitch Housing     |               |            |           |
| .XX: ± 0.15                              | .X° : ± 2.0°  | FINISH:<br>_____                  | DRAWING NO: | DR:Chen Quan Long                   | DATE:20/08/01 | PART NO:   |           |
| .XXX: ± 0.01                             | .XX° : ± 1.0° |                                   |             | CHKD: Wu Hui                        | DATE:20/08/01 | SCALE: N/A | PAGE: 1/1 |
|                                          |               |                                   |             | APPD:Ren An De                      | DATE:20/08/01 | UNITS: mm  | REV.: A   |