




Engineer Drawing

NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- 2.TERMINAL:PHOSPHOR BRONZE






3D VIEW



IPCB 08 371 F XX X X X

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series Type
- ② Pitch:0.8mm
- ③ Height
- ④ Connector Type
- ⑤ Pin Code:See Table 1
- ⑥ Rows Code
- ⑦ Serial Code
- ⑧ Other Code



RECOMMENDED P.C.BOARD LAYOUT

Table 1

Pin Code	NO.of contacts	Dimensions					
		A	B	C	D	E	F
40	40	21.80	15.20	17.60	20.20	18.80	20.15
50	50	25.80	19.20	21.60	24.20	22.80	24.15
60	60	29.80	23.20	25.60	28.20	26.80	28.15
80	80	37.80	31.20	33.60	36.20	34.80	36.15
A0	100	45.80	39.20	41.60	44.20	42.80	44.15
C0	120	53.80	47.20	49.60	52.20	50.80	52.15
E0	140	61.80	55.20	57.60	60.20	58.80	60.15
G0	160	69.80	63.20	65.60	68.20	66.80	68.15
I0	180	77.80	71.20	73.60	76.20	74.80	76.15
K0	200	85.80	79.20	81.60	84.20	82.80	84.15

TOLERANCES:
X.=±0.25
X.X=±0.20
X.XX=±0.10
GENERAL ANGLE
X°=±1°

ncp

www.i-ncp.com

PART NO:
IPCB08371F xx S7V

DRAWING NO
IPCB08371F07V

NAME:
0.8PH H3.7 BTB Female
Receptacle Assembly H5.0

SHEET 1 OF 1

UNITS:mm SCALE:1:1 REV.02