


1	2	3	4	5	6	7	8		
Dept	晨翔2.54mm FD插头, 10PIN, 黑色胶芯, 半金镍端子, 无Kink脚				REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
Qty					A	NEW RELEASE	JLZ 06/18/24'		
DC	1								
ED	1								
IE	1								
ISO	1								
PD	1								
R&D	1								
SD	1								
QA	1								
QC	1								
QF	1								

晨翔料号: DS1018-102BX

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use of this information in any format or manner. CONNELY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.



PCB孔位尺寸参考  
公差: ±0.05

备注:

1. 电性说明:
  - 1.1 接触阻抗: 20毫欧最大
  - 1.2 耐压: 600伏交流电一分钟
  - 1.3 绝缘阻抗: 1000兆欧最小
  - 1.4 额定电流: 3安
2. 环境特性:
  - 2.1 工作温度: -40~+105° C
3. 材料:
  - 3.1 端子: 黄铜, 焊接区镍底镀金
  - 3.2 胶芯: PBT, 黑色, 阻燃

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	I.D.C DIP PLUG PITCH 2.54mm	
X.	±0.60	X.	±5°	UNITS	mm	SHEET SIZE	A4	
.X	±0.38	.X	±3°			SERIES	DS1018 SERIES	
.XX	±0.25	.XX	±2°	<b>晨翔电子有限公司</b> <b>CONNELY CONNELY ELECTRONIC CO. LTD</b>				
DRAWING TYPE		CUSTOMER						
SCALE	1:1	SHEET	1 OF 1					
DRAWING NO.		C-DS1018-XXXXX-A						