

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use or modification is strictly prohibited without prior written consent from CONNELY. All intellectual properties provided herein are for reference purposes only and does not constitute authorization of its use in any format or manner. CONNELY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.

晨翔2.54mm FC三件式插头，26PIN，有上盖，黑色胶芯，半金镍端子

晨翔料号：DS1016-26MA2BB

REV. A DESCRIPTION NEW RELEASE DRAWN JLZ 12/01/21' CHECKED APPROVED

备注：
1. 电性说明：
1.1 接触阻抗：20毫欧最大
1.2 耐压：500伏交流电一分钟
1.3 绝缘阻抗：1000兆欧最小
1.4 额定电流：3安
2. 环境特性：
2.1 工作温度：-40~+105° C
3. 材料：
3.1 端子：黄铜，接触区镍底镀金
3.2 胶芯：PBT，黑色，阻燃

主体

上盖

端子

GENERAL TOLERANCE X. ±0.60 .X ±0.38 .XX ±0.25 ANGLE TOLERANCE X. ±5° .X ±3° .XX ±2° PROJECTION UNITS mm SHEET SIZE A4 TITLE I.D.C SOCKET PITCH 2.54mm SERIES DS1016 SERIES

DRAWING TYPE CUSTOMER SCALE 1:1 SHEET 1 OF 1 DRAWING NO. C-DS1016-XXXXX-A

CONNELY CONNELY ELECTRONIC CO. LTD