







NOTE:2
1. HOUSING MATERIAL: LCP, BLACK, UL94V-0.
2. TERMINAL MATERIAL: COPPER ALLOY (C2680),
Au:3u", Ni:50~120u".
3. SHELL MATERIAL: COPPER ALLOY (C5191),
Au:1~3u", Ni:50~120u".

3	GROUND CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
2	INNER CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
1	HOUSING	1	LCP UL94V-0		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARK



NOTE:1
1. ELECTRICAL CHARACTERISTICS:
1.1 CURRENT RATING: 0.5A MAX.
1.2 IMPEDANCE: 50OHM NOMINAL.
2. MECHANICAL CHARACTERISTICS:
2.1 OPERATING TEMP. -40°~90°
2.2 VEWR UP TO 3GHz:1.3MAX.
3GHz TO 6GHz:1.4MAX.
2.3 DURABILITY: 30CYCLES



制图	版次		比例		型号规格	HL2-IPEX1-SMT
审核	投 影					
批准	未标注公差的，以下列公差表为准				品名	SMT表贴式IPEX1代板端
	1. X. X±0.2 4. 去除锐边最大0.1 2. X. XX±0.1 5. 表面粗糙度Ra3.2 3. 角度±1° 6. 倒角C0.15MAX					
	* 为重点尺寸			单位	mm	
					 成都恒利泰科技有限公司 Chengdu HenryTech Technology co., Ltd	