










CUTAWAY VIEW



CUTAWAY VIEW




AFTER MATING

CONNECTOR
FRONT EDGE

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	SSTXp1	SSTXn1	VBUS	CC1	Dp1	Dn1	SBU1	VBUS	SSRXn2	SSRXp2	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND	SSRXp1	SSRXn1	VBUS	SBU2	Dn2	Dp2	CC2	VBUS	SSTXn2	SSTXp2	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First

1	SHELL	STAINLESS STEEL	NI PLATED
2	MID PLATE	STAINLESS STEEL	NI PLATED
3	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK UL 94 V-0
4	CONTACT	COPPER ALLOY	Au3u" PLATING ON CONTACT AREA
NO.	PARTS	MATERIAL	REMARKS



RoHS
Compliant
EU RoHS Standards



SCALE: 3:1

UNIT: mm

SIZE:

Unless otherwise
General Tolerance:

X.	
X.x	± 0.30
X.xx	± 0.25
X.xxx	± 0.15
Angles	$\pm 1^\circ$

Title: Flag Type-c 24P Female
SMT Pad UP2.73 CH=7.2 L=13.9mm

Molde Code: GT-USB-7092C

DRAWN

CHECKE

APPROVED

DATE _____

品贊科技
b-Switch
www.dg-switch.com

REV: A0

SHEET: 1/1