












RECOMMENDED PCB LAYOUT
TOLERANCE $\pm 0.05\text{mm}$

1	SHELL	STAINLESS STEEL	Ni PLATED
2	MID PLATE	STAINLESS STEEL	Ni PLATED
3	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK UL 94 V-0
4	TERMINALS	COPPER ALLOY	Au PLATING ON CONTACT AREA
NO.	PARTS	MATERIAL	REMARKS



RoHS
Compliant
EU RoHS Standards



A4	
----	--

X.	
X.x	± 0.30
X.xx	± 0.25
X.xxx	± 0.15
Angles	$\pm 1^\circ$

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2023.01.3



REV: A0	SHEET: 1/1
---------	------------