

0603贴片电容本

YPB-C0603 系列

89 种型号，每种 25 颗，一共 2475 颗，其中 0.1uF 常用电容 275 个，清单如下：

	体积	容量	电压	精度	材质
1	C0603	0.5PF	50V	±0.25PF	COG/NP0
2	C0603	1PF	50V	±0.25PF	COG/NP0
3	C0603	1.5PF	50V	±0.25PF	COG/NP0
4	C0603	1.8PF	50V	±0.25PF	COG/NP0
5	C0603	2PF	50V	±0.25PF	COG/NP0
6	C0603	2.2PF	50V	±0.25PF	COG/NP0
7	C0603	2.4PF	50V	±0.25PF	COG/NP0
8	C0603	2.7PF	50V	±0.25PF	COG/NP0
9	C0603	3PF	50V	±0.25PF	COG/NP0
10	C0603	3.3PF	50V	±0.25PF	COG/NP0
11	C0603	3.6PF	50V	±0.25PF	COG/NP0
12	C0603	3.9PF	50V	±0.25PF	COG/NP0
13	C0603	4.3PF	50V	±0.25PF	COG/NP0
14	C0603	4.7PF	50V	±0.25PF	COG/NP0
15	C0603	5PF	50V	±0.25PF	COG/NP0
16	C0603	5.1PF	50V	±0.5PF	COG/NP0
17	C0603	5.6PF	50V	±0.5PF	COG/NP0
18	C0603	6PF	50V	±0.5PF	COG/NP0
19	C0603	6.2PF	50V	±0.5PF	COG/NP0

20	C0603	6.8PF	50V	±0.5PF	COG/NP0
21	C0603	7PF	50V	±0.5PF	COG/NP0
22	C0603	7.5PF	50V	±0.5PF	COG/NP0
23	C0603	8PF	50V	±0.5PF	COG/NP0
24	C0603	8.2PF	50V	±0.5PF	COG/NP0
25	C0603	9PF	50V	±0.5PF	COG/NP0
26	C0603	10PF	50V	±5%	COG/NP0
27	C0603	12PF	50V	±5%	COG/NP0
28	C0603	13PF	50V	±5%	COG/NP0
29	C0603	15PF	50V	±5%	COG/NP0
30	C0603	18PF	50V	±5%	COG/NP0
31	C0603	20PF	50V	±5%	COG/NP0
32	C0603	22PF	50V	±5%	COG/NP0
33	C0603	24PF	50V	±5%	COG/NP0
34	C0603	27PF	50V	±5%	COG/NP0
35	C0603	30PF	50V	±5%	COG/NP0
36	C0603	33PF	50V	±5%	COG/NP0
37	C0603	36PF	50V	±5%	COG/NP0
38	C0603	39PF	50V	±5%	COG/NP0
39	C0603	43PF	50V	±5%	COG/NP0
40	C0603	47PF	50V	±5%	COG/NP0
41	C0603	51PF	50V	±5%	COG/NP0
42	C0603	56PF	50V	±5%	COG/NP0
43	C0603	62PF	50V	±5%	COG/NP0

44	C0603	68PF	50V	± 5%	COG/NP0
45	C0603	75PF	50V	± 5%	COG/NP0
46	C0603	82PF	50V	± 5%	COG/NP0
47	C0603	91PF	50V	± 5%	COG/NP0
48	C0603	100PF	50V	± 5%	COG/NP0
49	C0603	110PF	50V	± 5%	COG/NP0
50	C0603	120PF	50V	± 5%	COG/NP0
51	C0603	130PF	50V	± 5%	COG/NP0
52	C0603	150PF	50V	± 5%	COG/NP0
53	C0603	160PF	50V	± 5%	COG/NP0
54	C0603	180PF	50V	± 5%	COG/NP0
55	C0603	200PF	50V	± 5%	COG/NP0
56	C0603	220PF	50V	± 10%	X7R
57	C0603	270PF	50V	± 10%	X7R
58	C0603	330PF	50V	± 10%	X7R
59	C0603	390PF	50V	± 10%	X7R
60	C0603	470PF	50V	± 10%	X7R
61	C0603	560PF	50V	± 10%	X7R
62	C0603	680PF	50V	± 10%	X7R
63	C0603	820PF	50V	± 10%	X7R
64	C0603	1nF	50V	± 10%	X7R
65	C0603	1. 2nF	50V	± 10%	X7R
66	C0603	1. 5nF	50V	± 10%	X7R
67	C0603	1. 8nF	50V	± 10%	X7R

68	C0603	2. 2nF	50V	± 10%	X7R
69	C0603	2. 7nF	50V	± 10%	X7R
70	C0603	3. 3nF	50V	± 10%	X7R
71	C0603	3. 9nF	50V	± 10%	X7R
72	C0603	4. 7nF	50V	± 10%	X7R
73	C0603	5. 6nF	50V	± 10%	X7R
74	C0603	6. 8nF	50V	± 10%	X7R
75	C0603	8. 2nF	50V	± 10%	X7R
76	C0603	10nF	25V	± 10%	X7R
77	C0603	15nF	25V	± 10%	X7R
78	C0603	22nF	25V	± 10%	X7R
79	C0603	33nF	16V	± 10%	X7R
80	C0603	47nF	16V	± 10%	X7R
81	C0603	68nF	16V	± 10%	X7R
82	C0603	82nF	16V	± 10%	X7R
83	C0603	100nF	16V	± 10%	X7R
84	C0603	220nF	16V	± 10%	X7R
85	C0603	470nF	16V	± 10%	X5R
86	C0603	680nF	10V	± 10%	X5R
87	C0603	1uF	10V	± 20%	X5R
88	C0603	2. 2uF	6. 3V	± 20%	X5R
89	C0603	4. 7uF	6. 3V	± 20%	X5R