

2.4&5.8GHz FPC Antenna

FEATURES



- Welding RG 1.13 cable, Ipex connector, 3M sticker for easy installation.
- For smart device wireless, Zigbee, Bluetooth terminal wireless receiving antenna transmitter antenna

PRODUCTS

Part No.	Weight	Dimensions (L x WxH)	Cables Dimensions	Connector	Color
AIWF014	0.43g	FPC:21.8*18.2*0.2mm	Φ 1.13*120mm	IPX1	Black+yellow

SPECIFICATIONS

PARAMETER	SPECIFICATION
Frequency Bands, MHz	2400-2500; 5100-5800
VSWR (Max)	3.0:1
Nominal Impedance	50 Ω
Max Power (ambient temp of 25°C)	10 Watts
Azimuth Beam Width (deg)	Omnidirectional
Polarization	Linear, Omnidirectional
Color	Black+yellow
Storage Temperature Range (°C)	-40° C to +85° C
Operational Temperature Range (°C)	-40° C to +85° C
Material Substance Compliance	REACH/RoHS Compliant
HSCODE	8517707090
USHSCODE	8517620010
UPC	


MyAntenna RF Technology Co., Ltd

ADD: No.RM 405, R3-A Building, Shenzhen High-Tech Park, Nanshan, Shenzhen, P.R. China.


TEL: +86-0755-86503881 FAX: +86-0755-27801677 E-mail: nfc@imyantenna.com


ELECTRICAL DATA

Return Loss





Efficiency (%)






Peak Gain (dBi)






RADIATION PATTERNS

2D Radiation Pattern at 2450MHz



2D Radiation Pattern at 5500MHz



HOUSING CONFIGURATIONS

