

## Important Note

This cable can only be used to stream 4K video when used with a Thunderbolt-3 enabled monitor. A USB-C or DisplayPort input will not support video transmission.

# Thunderbolt 3 Active Cable (M/M) - 40 Gbps, 5A 100W Power Delivery, 4K/60 Hz, 1M (3.28 ft.), Black

MODEL NUMBER: MTB3-01M-5A-AB



Connects 2 Thunderbolt 3 devices, including MacBooks and Chromebooks, for charging them or transmitting 4K video at 40 Gbps speeds.

## Features

**Active Cable Connects Thunderbolt 3 Devices, Including MacBooks and Chromebooks** This Thunderbolt 3 cable allows you to connect one Thunderbolt 3-enabled device to another, including MacBooks, Ultrabooks, Chromebooks, external hard drives and docking stations. It transmits full 4K x 2K (3840 x 2160 at 60 Hz) DisplayPort video when used with Thunderbolt 3-enabled monitors. The cable's one-meter length makes it easy to carry in your briefcase or laptop bag for quick video connections and file transfers on the go.

**Charges Devices and Transfers Data 4 Times Faster Than USB 3.1 Gen 2** The MTB3-01M-5A-AB supports bidirectional Thunderbolt 3 data transfer speeds up to a sizzling 40 Gbps, which is four times as fast as USB 3.1 Gen 2, making it an ideal cable for downloading 4K video files and transmitting them to a 4K monitor or television with a Thunderbolt 3-enabled input. Transceivers in each connector regulate the transfer of data throughout the entire length of the active cable. The PD Charging 2.0 cable also provides power output up to 5 amps (100 watts), which is sufficient for fast-charging, syncing and powering most large-capacity devices.

**Reversible Thunderbolt 3 Connectors Attach in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible Thunderbolt 3 male connectors plug into a Thunderbolt 3 or USB-C port in either direction for a fumble-free connection every time. Note: both ends must be connected to a Thunderbolt 3 port to achieve 40 Gbps transfer speeds.

## Specifications

### Highlights

- Thunderbolt 3 cable is compatible with all USB-C and Thunderbolt 3 devices
- Supports Thunderbolt 3 speeds up to 40 Gbps—4x faster than USB 3.1 Gen 2
- Provides 5A (100W) power output for charging and powering large-capacity mobile devices
- Reversible Thunderbolt 3 plugs connect in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port
- Bridge two Thunderbolt 3-enabled notebooks for migrating data or setting up a peer-to-peer network
- Stream 4K video from your MacBook or Chromebook to a monitor or television with a Thunderbolt 3-enabled input
- Connect a DisplayPort monitor or laptop to an external GPU box for playing graphics-intensive 4K video games

### System Requirements

- Devices with Thunderbolt 3 or USB-C ports (40 Gbps speeds possible only through Thunderbolt 3)

### Package Includes

- MTB3-01M-5A-AB Thunderbolt 3 Cable, M/M, 1 m, Black



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

UPC Code	037332242006
Technology	Thunderbolt
<b>POWER</b>	
Power Consumption (Watts)	1.5
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
<b>CONNECTIONS</b>	
Side A - Connector 1	THUNDERBOLT 3 (Type-C MALE)
Side B - Connector 1	THUNDERBOLT 3 (Type-C MALE)
Connector Plating	Nickel
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Outer Diameter (OD)	+/- 4.75 mm
Cable Length (ft.)	3.3
Cable Length (m)	1.01
Cable Length (in.)	39.4
Cable Length (cm)	100
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	25% ~ 85% RH
Power Provided to Connected Device(s)	5A (100W) Power Delivery
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	40 Gbps
High Voltage	No
Locking Plug	No
Displayport Specification	1.2
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL Listed
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)

WARRANTY & SUPPORT

Product Warranty Period (International)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.