

Specification Sheet

Part Number: 166-11808

- Double slit opening offers easy access during installation and maintenance.
- Material is easy to use and cut; reduces installation time and labor costs.
- Flexible, abrasion resistant and durable for a variety of applications.
- Good impact strength; recovers quickly if crushed.
- UV resistant; suitable for use in outdoor applications.
- Offered in fine or coarse corrugated pitch.



HelaGuard Non-Metallic Conduit, Double Slit, Std Wt, 0.38" Dia, Nylon PA6, Black, 164 ft/Std. Reel

Article Number 166-11808

Type HG-DC0380

Color Black (BK)

Quantity Per reel

Product Description A standard-weight corrugated conduit with two slit openings that eases installation and maintenance of wire and cable bundles. The interlocking construction is excellent for retrofitting projects. PA6 material is highly resistant to solvents and oils, and offers UV and abrasion resistance.

Short Description	HelaGuard Non-Metallic Conduit, Double Slit, Std Wt, 0.38" Dia, Nylon PA6, Black, 164 ft/Std. Reel
Global Part Name	HG-DC0380-PA6-BK
Length L (Imperial)	164.0
Length L (Metric)	50
Inner Diameter D (Imperial)	0.41
Inner Diameter D (Metric)	10.3
Outside Diameter OD (Imperial)	0.63
Outside Diameter OD (Metric)	15.8
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	16
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	EN IEC 61386
Halogen Free	Yes

UV Resistant (Yes/No)

No

Operating Temperature

-40°F to +248°F (-40°C to +120°C)

Reach Compliant (Article 33)

Yes

ROHS Compliant

Yes

Package Quantity (Imperial)

164.0

Package Quantity (Metric)

50

Customs Number

3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)