



Part Number : 1200845107

Series Number : 120025

Product Category : Circular Industrial Connectors

Product Description : Ultra-Lock (M12) Receptacle, 4 Poles, M16x1.5 Mounting Threads, Female (Straight) to 0.34mm² PVC Leads, 0.30m (11.81") Length

Status : Active

Engineering Number : WR4U20E03C3003

Documents & Resources

Drawings
Drawing 1200845107_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120025
Description	Ultra-Lock (M12) Receptacle, 4 Poles, M16x1.5 Mounting Threads, Female (Straight) to 0.34mm ² PVC Leads, 0.30m (11.81") Length
IP Rating	IP69K
NEMA Rating	NEMA 6
Product Family	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Type	Single Ended (pigtail)
UPC	883906778804

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Net Weight	198.200/g
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 1569
Wire Size (AWG)	22

This document was generated on Apr 12, 2024