

# GSC550M09010D

电池连接器

90°弯头

电性能	
额定耐压	16VDC
额定电流	10A
尺寸规格	
长	27.00±0.2mm
宽	15.5±0.2mm
PIN 间距	5.0mm, 5PIN
材料	
连接体	铜镀金
本体	塑胶 UL94V-0

RoHS Compliant									
				2023.09.07					
				文件受控					
								<b>SPECIFICATIONS</b> 1. ELECTRICAL CHARACTERISTICS: 1-1. RATING: DC 16V 10A 1-2. CONTACT RESISTANCE: 30mΩ MAX (INITIAL) 1-3. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR ONE MINUTE 1-4. INSULATION RESISTANCE: 500MΩ MIN, MEASURED BY 500V DC 2. LIFE TEST: MECHANICAL LIFE TEST 5,000 CYCLES. 3. TEMPERATURE RISE : 30° C MAX	
		2 HOUSING PA9T		1 BLACK					
		1 CONTACT TERMINAL C2680		5 Au PLATED					
		NO. PARTS		MATERIAL		QTY. FINISHING			
<b>深圳市圭石南方科技发展有限公司</b> PART NAME: CONNECTOR PART NO.: GSC550M09010D DRAWING: Y. C. Zhang CHECK: G. C. Chen DWG. No.: REV.: A1 UNIT: mm TOLERANCE: ±0.10 ±0.15 ±0.20 ±0.25 ±0.30 ±0.40 ±0.50 OTHERWISE: ±0.10 ±0.15 ±0.20 ±0.25 ±0.30 ±0.40 ±0.50 ANGLE: 0° ±3° APPROVAL: SCALE: 3:1 DATE: 06-06-2018 PAGE: 1 OF 1									
COPYRIGHT RESERVED, PLEASE DO NOT COPY.									