

Specification Sheet

Part Number: 156-00444



An all-in-one bundling and fastening solution that saves time and reduces costs.

Foam seal prevents ingress of moisture and debris and prevents vibration.

1-Pc Cable Tie/Arrowhead Mount with Seal, 8.5" Long, 50lb Tensile, PA66HIRHS, Natural, 500/bg

Article Number	156-00444
----------------	-----------

Type	T50ROSAH6MDU
------	--------------

Color	Natural (NA)
-------	--------------

Quantity Per	bag
--------------	-----

Product Description	The arrowhead design of these ties offers a low insertion force and a high extraction force. The foam rubber seal provides additional protection against moisture and debris. One-piece mounting ties offer a complete solution by simultaneously bundling and mounting cables, wires and hoses.
---------------------	--

Short Description	1-Pc Cable Tie/Arrowhead Mount with Seal, 8.5" Long, 50lb Tensile, PA66HIRHS, Natural, 500/bg
-------------------	---

Global Part Name	T50ROSAH6MDU-PA66HIRHS-NA
------------------	---------------------------

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.5
Length L (Metric)	216.0
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.2
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0
Panel Thickness Min (Imperial)	0.03

Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	2.1
Mounting Hole Diameter D (Imperial)	0.24 - 0.26
Mounting Hole Diameter D (Metric)	6.2 - 6.6 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.6
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)