



PCB Layout recommended



Circuit diagram

NO.1	
PART NO	H
A	3.5
B	3.8

NO.2	
PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

PART NO.	
K2-1112SA	K2-1112SN

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
				2	Phosphor Bronze	Plating silver
⑤	Terminal					
④	Contact					
③	Base					
②	Cover					
①	Keystoke					

APPROVALS		DATE	TITLE:	TACT SWITCHS		
DRAWN	JKUN.LU	2015.3.28		PART NO.	K2-1112SD-□□□W-□□	
CHECKED						
APPROVALS						

TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20				
	5~10	±0.15	±2°			
	~ 5	±0.10				

ECN NO.	REV.	DATE.	NEW	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	DRAWING NO.	SHEET 1 OF 1