

# USB-C to Mini DisplayPort Active Adapter Cable (M/M), 4K 60 Hz, Black, 6 ft. (1.8 m)

MODEL NUMBER: U444-006-MDP



Connects your existing Mini DisplayPort (mDP) monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, smartphone or PC. Saves you the clutter and expense of additional cables, adapters and displays.

## Features

**Connects a Mini DisplayPort Display to Your USB-C or Thunderbolt 3 Device**Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate ModeIdeal for giving video presentations, editing multiple documents, or streaming 4K video for digital signageSupports USB 3.1 Gen 1 data transfer rates up to 5 GbpsSupports DisplayPort 1.2 specificationsExtend 4K video from your primary display to another, duplicate the same video on both, or convert a secondary display to be the primary display

**Crystal-Clear 4K Video and Digital Audio**Supports UHD video resolutions up to 3840 x 2160 (4K) @ 60 HzSupports 36-bit Deep Color (12 bits per channel)Supports per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR)

**Reversible USB-C Connector**Fumble-free reversible USB-C plug connects in either direction for quick connection every time

**Premium Construction**Gold-plated connectors and contacts for maximum conductivity and minimum data lossFoil and braid shielding protects against EMI/RFI line noise that can distort or destroy dataIntegral strain relief helps cable and connectors move freely without stress or crackingDurable PVC jacket designed to last a long time

**Ready for Instant Use**Plug-and-play operation with no software, drivers or external power required6 ft. length easy to manage in crowded environmentsBackward compatible with non-4K displays

## Specifications

OVERVIEW	
UPC Code	037332193841
Product Type	Active Cable
Technology	DisplayPort

## Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports UHD video resolutions up to 4K @ 60 Hz
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

## System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with Mini DisplayPort input

## Package Includes

- U444-006-MDP USB 3.1 Gen 1 USB-C to Mini DisplayPort 4K Adapter Cable (M/M), 6 ft.



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

Cable Type	Active
<b>VIDEO</b>	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
HDR Support	Yes
<b>INPUT</b>	
Bus Powered	Yes
Product Length (in.)	72
Product Length (cm.)	182.88
Product Length (ft.)	6
Product Length (m)	1.83
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	No
<b>POWER</b>	
Power Consumption (Watts)	0.6
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MINI DISPLAYPORT (MALE)
Connector Plating	Gold
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PVC, ABS
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.19
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Unit Packaging Type	Polybag



Powering Business Worldwide



Unit Weight (lbs.)	0.18
Unit Weight (kg)	0.08
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	2.1 BTU/Hr
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Displayport Specification	1.2
HDCP Specification	1.3
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.