



借用登记

旧底图总号

底图总号




签字

日期





技术要求:

- 1、塑件材料: LCP (UL-94V-0)
- 2、接触件: 黄铜镀锡
- 3、接触电阻: $\leq 30\text{m}\Omega$
- 4、绝缘电阻: $\geq 1000\text{M}\Omega$
- 5、额定电压: 250V AC DC
- 6、额定电流: 7.0A AC DC
- 7、耐压: 能承受1000V AC/Minute
- 8、工作温度: $-25^{\circ}\sim+85^{\circ}$
- 9、可焊性试验: 浸锡面积 $\geq 95\%$ 温度260,时间 2.5 ± 0.5 秒
- 10、铅和镉等六大有害物质含量要符合环保要求



Pin	A	B	C
2	3.96	9.8	8.6
3	7.92	13.76	12.56
4	11.88	17.72	16.52
5	15.84	21.68	20.48
6	19.8	25.64	24.44
7	23.76	29.6	28.4
8	27.72	33.56	32.36
9	31.68	37.52	36.32
10	35.64	45.44	40.28



3	弹片 Fitting Nail	黄铜	2	电镀层: 整个表面镀层30u"MIN,厚度等 80u"MIN.
2	端子 Contact	黄铜	n×1	电镀层: 整个表面镀层30u"MIN,厚度等 80u"MIN.
1	基板 Wafer	LCP (UL94V-0)	1	材料
序号	名称	材料	数量	附注

GENERAL TOLERANCES			DRAWN BY 绘图者		深圳市钜硕电子有限公司		
0.X ±0.25	X.° ±3°		CHK. BY 审核者				
0.XX ±0.12			APRV. BY 批准人		SHEET	PROD. NAME	
0.XXX ±0.05	X.X° ±0.5°		DRAWING NO.		10P1	PART NO.	VH396-S**DCA-00
UNIT	SIZE	SCALE			TITLE VH3.96mm 卧式贴片		
MM	A4	1:1					