






3D VIEW




RECOMMENDED PCB PATTERN DIM.
TOLERANCE : ±0.05

NOTES:

- 1.HUOSING: PA9T HIGH-TEMP THERMOPLASTIC U94V-0 COLOR:BLACK
- 2.TERMINAL:PHOSPHOR BRONZE
- PLATING:1" GOLD FLASH OVERALL 50~100" NICKEL UNDER PLATED.

3.CODING INFORMATION:



MATING HEIGHT (H.)	PLUG (H.)	SOCKET (H.)	NO. of contacts	Dimensions					NO. of contacts	Dimensions				
				A	B	C	D	E		A	B	C	D	
7.0		3.0		3.70	0.50	1.50	2.40		2*27	16.20	13.00	14.00	14.90	
				4.20	1.00	2.00	2.90		2*28	16.70	13.50	14.50	15.40	
7.5		3.5		4.70	1.50	2.50	3.40		2*29	17.20	14.00	15.00	15.90	
				5.20	2.00	3.00	3.90		2*30	17.70	14.50	15.50	16.40	
8.0		4.0		5.70	2.50	3.50	4.40		2*31	18.20	15.00	16.00	16.90	
				6.20	3.00	4.00	4.90		2*32	18.70	15.50	16.50	17.40	
8.5		4.5		6.70	3.50	4.50	5.40		2*33	19.20	16.00	17.00	17.90	
				7.20	4.00	5.00	5.90	4.00	2*34	19.70	16.50	17.50	18.40	
				7.70	4.50	5.50	6.40		2*35	20.20	17.00	18.00	18.90	
				8.20	5.00	6.00	6.90		2*36	20.70	17.50	18.50	19.40	
				8.70	5.50	6.50	7.40		2*37	21.20	18.00	19.00	19.90	
				9.20	6.00	7.00	7.90		2*38	21.70	18.50	19.50	20.40	
				9.70	6.50	7.50	8.40		2*39	22.20	19.00	20.00	20.90	
				10.20	7.00	8.00	8.90		2*40	22.70	19.50	20.50	21.40	
				10.70	7.50	8.50	9.40		2*41	23.20	20.00	21.00	21.90	
				11.20	8.00	9.00	9.90		2*42	23.70	20.50	21.50	22.40	
				11.70	8.50	9.50	10.40		2*43	24.20	21.00	22.00	22.90	
				12.20	9.00	10.00	10.90		2*44	24.70	21.50	22.50	23.40	
				12.70	9.50	10.50	11.40		2*45	25.20	22.00	23.00	23.90	
				13.20	10.00	11.00	11.90		2*46	25.70	22.50	23.50	24.40	
				13.70	10.50	11.50	12.40	8.00	2*47	26.20	23.00	24.00	24.90	
				14.20	11.00	12.00	12.90		2*48	26.70	23.50	24.50	25.40	
				14.70	11.50	12.50	13.40		2*49	27.20	24.00	25.00	25.90	
				15.20	12.00	13.00	13.90		2*50	27.70	24.50	25.50	26.40	
				15.70	12.50	13.50	14.40							

8.00

深圳市连欣科技有限公司




一般公差
GENERAL TOLERANCE
X ±0.25
Y ±0.25
Z ±0.10
ANGLES ±1°
品名(TITLE): 0.5mm 双槽BTB PLUG

制图 (DR):
审核 (CHK):
批准 (APP):

料号 (PART NO.): XDBM-05**-2*N P
比例 (SCALE): 1:1
图幅 (SIZE): A4
单位 (UNITS): mm

版本 A
1 OF 1

比例 (SCALE): 1:1
图幅 (SIZE): A4
单位 (UNITS): mm







NOTES:

1.HOUSING: PA9T HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
2.TERMINAL:PHOSPHOR BRONZE
PLATING:1" GOLD FLASH OVERALL 50~100" NICKEL UNDER PLATED.

3.CODING INFORMATION: XDBF-05**-2*N P

LIANXIN BTB CONNECTOR SERIES
BOARD TO BOARD MALE
0.5 SPACING
MATING HEIGHT
70---7.0 height
75---7.5 height
80---8.0 height
85---8.5 height



PLUG HEIGHT (H)	SOCKET (H)	NO. of contacts	Dimensions					NO. of contacts	Dimensions				
			A	B	C	D	E		A	B	C	D	E
7.0	3.0		3.70	0.50	1.56	2.40		2*27	16.20	13.00	14.06	14.90	
7.5	3.5		4.20	1.00	2.06	2.90		2*28	16.70	13.50	14.56	15.40	
8.0	4.0		4.70	1.50	2.56	3.40		2*29	17.20	14.00	15.06	15.90	
8.5	4.5		5.20	2.00	3.06	3.90		2*30	17.70	14.50	15.56	16.40	
		2*6	5.70	2.50	3.56	4.40		2*31	18.20	15.00	16.06	16.90	
		2*7	6.20	3.00	4.06	4.90		2*32	18.70	15.50	16.56	17.40	
		2*8	6.70	3.50	4.56	5.40		2*33	19.20	16.00	17.06	17.90	
		2*9	7.20	4.00	5.06	5.90		2*34	19.70	16.50	17.56	18.40	
		2*10	7.70	4.50	5.56	6.40		2*35	20.20	17.00	18.06	18.90	
		2*11	8.20	5.00	6.06	6.90		2*36	20.70	17.50	18.56	19.40	
		2*12	8.70	5.50	6.56	7.40		2*37	21.20	18.00	19.06	19.90	
		2*13	9.20	6.00	7.06	7.90		2*38	21.70	18.50	19.56	20.40	
		2*14	9.70	6.50	7.56	8.40		2*39	22.20	19.00	20.06	20.90	
		2*15	10.20	7.00	8.06	8.90		2*40	22.70	19.50	20.56	21.40	
		2*16	10.70	7.50	8.56	9.40		2*41	23.20	20.00	21.06	21.90	
		2*17	11.20	8.00	9.06	9.90		2*42	23.70	20.50	21.56	22.40	
		2*18	11.70	8.50	9.56	10.40		2*43	24.20	21.00	22.06	22.90	
		2*19	12.20	9.00	10.06	10.90		2*44	24.70	21.50	22.56	23.40	
		2*20	12.70	9.50	10.56	11.40		2*45	25.20	22.00	23.06	23.90	
		2*21	13.20	10.00	11.06	11.90		2*46	25.70	22.50	23.56	24.40	
		2*22	13.70	10.50	11.56	12.40		2*47	26.20	23.00	24.06	24.90	
		2*23	14.20	11.00	12.06	12.90		2*48	26.70	23.50	24.56	25.40	
		2*24	14.70	11.50	12.56	13.40		2*49	27.20	24.00	25.06	25.90	
		2*25	15.20	12.00	13.06	13.90		2*50	27.70	24.50	25.56	26.40	
		2*26	15.70	12.50	13.56	14.40							

深圳市连欣科技有限公司

GENERAL TOLERANCE 0.5mm 双槽BTB SOCKET

料号(PART NO): XDBF-05**-2*N P

版本 A 比例(SCALE) 图幅(SIZE) 张数(SHEET) 单位

审核(CHKD): 2018.03.3

批准 (APPD):