


<i>P1</i>		<i>P2</i>
<i>L</i>	—————	3 白
<i>N</i>	—————	1 黑

WITE LIST

					TOLERANCE UNLESS SPECIFIED																				
					UP TO 5mm: ±0.1	ANGULAR ±1°																			
					ABOVE 5mm: ±0.2		NO	DATE	REVISIONS			BY	APPD												
5	PIPE	HEAT SHRINKABLE TUBING	2	BLACK	TITLE:DC JACK				UNIT : MM	ROHS	DWN														
4	CONTACT FOOT	BRASS	2	Ag PLATED	MODEL:DC-018Ø2.0-SH024				SCALE: 4:1	COMPLIANT	CHK'D														
3	HOUSING	PA66	1	WHITE	东莞市六钧电子五金有限公司									APPD											
2	CONN.	DC-005LØ2.0mm	1																						
1	ELECTRIC WIRE	PVC	2	BLACK/WHITE																					
NO.	PART NAME	MATERIAL	QTY	FINISHING										PRO.AGL:			REV :AC								