





A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		



Part No	Pin	A	B
WF-1D396A2P	2	3.96	8.07
WF-1D396A3P	3	7.92	12.03
WF-1D396A4P	4	11.88	15.99
WF-1D396A5P	5	15.84	19.95
WF-1D396A6P	6	19.8	23.91
WF-1D396A7P	7	23.76	27.87
WF-1D396A8P	8	27.72	31.83
WF-1D396A9P	9	31.68	35.79
WF-1D396A10P	10	35.64	39.75
WF-1D396A11P	11	39.6	43.71
WF-1D396A12P	12	43.58	47.67

技术参数:
 PIN数: 2~12
 适用线规: AWG22#~18#
 适用基板厚度: 1.6mm
 温度范围: -25℃~85℃
 额定电压: 250V AC/DC
 额定电流: 7.5A
 接触电阻: ≤0.015 Ω
 绝缘电阻: ≥1000N Ω
 耐压: 1500V AC/minute
 材料: (Nylon)66UL94V-2(0)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				 
DIM.	TOL.	TITLE: VH3.96MM HOUSING				
X		DWG. NO.: WF-1D396ANP		DRAWN: MAX		
X.X	±0.30	PART NO.: WF-1D396ANP		CHECKED: ELLA		
X.XX	±0.25	UNIT: mm		SCALE: none	SHEET: 1 of 1	
X.XXX	±0.15	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL		
GENERAL ANGLE: ±3°						