





PIN	$\phi 1.65$	$\phi 2$	$\phi 2.5$
X	1.2	1.0	0.75
APPD			

HAO YU



P.C.B LAYOUT

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		A2 2020.07.15	△ 更新PCB板开孔图尺寸标注		GYW	
						UP TO 5mm: ±0.1	ANGULAR ±1°		A1 2018.10.10	△ 新增尺寸管控		
5	DC044 PING	BRASS	1	Ni PLATED		UP TO 5mm: ±0.1	ANGULAR ±1°	A0 2013.8.27		初版	liu	
4	DC044 2#SPRING	SUS/PBS	1	Ag PLATED		TITLE:DC JACK MODEL: DC-044 1.65-SU		NO	DATE	REVISIONS		APPD
3	DC044 3#CURVE PIECE	BRASS	1	Ag PLATED				A0	2013.8.27	ROHS	DWN	
2	DC044 4#FLAT PIECE	BRASS	1	Ag PLATED		UNIT : MM SCALE: 5:1		NO	DATE	COMPLIANT	CHK'D	
1	DC044 CASE	PBT/PA9T	1	BLACK				A0	2013.8.27	APPD		
										PRO.AGL:	REV :A2	

东莞市六钧电子五金有限公司